

# KALLISTA®

## Script® Decorative by KALLISTA Sink faucet, low spout, White Porcelain knob handles P25056-CMC

### Features

- Handcrafted porcelain handles
- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- Spout reach is 5-1/2" (140 mm)
- Aerated flow
- Includes soft-touch drain
- 1.2 gpm (4.5 lpm) maximum flow rate

### Recommended Products/Accessories

- P74241-WO Under-mount Sink, Soft Oval with Overflow, Glazed
- P25051-SLC Sink faucet, arch spout, clear crystal knob handles
- P25041-00 Towel Bar, 24"
- P25046-00 Hook



### Codes/Standards







- ASME A112.18.1/CSA B125.1
- NSF/ANSI/CAN 61
- NSF/ANSI/CAN 372
- DOE - Energy Policy Act 1992
- EPA WaterSense®
- California Energy Commission (CEC)

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BCH	Blush Bronze
	BAF	Brushed French Gold
	BN	Brushed Nickel
	BV	Brushed Bronze
	SN	Polished Nickel

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

2-15-2025 21:53 - US

# KALLISTA

Script® Decorative by KALLISTA  
Sink faucet, low spout, White Porcelain knob  
handles  
P25056-CMC



## Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with  
overflow: Yes

Spout:

Spout reach: 5-1/8" (130 mm)

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

2-15-2025 21:53 - US