

KALLISTA.

One™ by KALLISTA
Deck-Mount Bridge Kitchen Faucet, Lever
Handles
P25202-LV

Features

- A selection of products within this collection is in stock and ready to ship. Please visit kallista.com/resources#ReadyToShip for the complete list of Ready-to-Ship products and finishes
- High-quality solid-brass construction for durability and reliability
- Spout reach is 8" (203 mm)
- 1.8 gpm (6.8 lpm) maximum flow rate
- Two-hole installation
- 360-degree swing spout
- Sink strainer with tailpiece sold separately
- CP, AG, GN finishes on this product are PVD (Physical Vapor Deposition) coated

Recommended Products/Accessories

P23148-LV Contemporary filter faucet
L20309-00 Stainless Steel Kitchen Sink with Deluxe
Accessories
P25215-00 Soap/Lotion Dispenser
P34014-00 Air Gap Body With Cover



ADA

Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	AD	Nickel Silver
	CP	Polished Chrome
	AG	Brushed Nickel
	GN	Gunmetal
	BL	Matte Black
	ULB	Unlacquered Brass
	BGP	Brushed Graphite
	PGP	Polished Graphite
	2MB	Brushed Moderne Brass

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

1-26-2026 20:59 - US

KALLISTA.

One™ by KALLISTA
Deck-Mount Bridge Kitchen Faucet, Lever
Handles
P25202-LV



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.8 gal/min (6.8 l/min)

Spout:

Spout reach: 8" (203 mm)

Notes

ADA compliant when installed to the specific requirements of these regulations.