

KALLISTA®

One™ by KALLISTA
Single-control bidet faucet
P26614-00

Features

- High-quality solid metal construction for durability and reliability
- Swivel spray aerator
- Spout reach is 4-7/8" (124 mm)
- 6-11/16" (170 mm) faucet height
- 1.5 gpm (5.7 lpm) minimum flow rate at 20 psi (1.4 bar)
- Includes metal pop-up drain with 1-1/4" metal tailpiece
- Single-hole installation

Recommended Products/Accessories

P24409-00 Single-control sink faucet
P34408-00 Toilet Paper Holder
P34410-00 Towel Ring
P74053-00



Codes/Standards






ASME A112.18.1/CSA B125.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	BAF	Brushed French Gold
	BN	Brushed Nickel
	SN	Polished Nickel
	2MB	Brushed Moderne Brass

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

2-28-2025 22:39 - US

KALLISTA

One™ by KALLISTA
Single-control bidet faucet
P26614-00



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.5 gal/min (5.7 l/min)

Drain included: Yes

Spout:

Spout reach: 4-7/8" (124 mm)

Handshower rated max flow: 1.5 gal/min (5.7 l/min)

Notes

Install this product according to the installation instructions.