

# KALLISTA®

## One™ by KALLISTA Single-control bidet faucet P26614-00

### Features

- High-quality solid metal construction for durability and reliability
- Swivel spray aerator
- Spout reach is 4-7/8" (124 mm)
- 6-11/16" (170 mm) faucet height
- 1.5 gpm (5.7 lpm) minimum flow rate at 20 psi (1.4 bar)
- Includes metal pop-up drain with 1-1/4" metal tailpiece
- Single-hole installation

### Recommended Products/Accessories

P24409-00 Single-control sink faucet  
P34408-00 Toilet Paper Holder  
P34410-00 Towel Ring  
P74053-00



### Codes/Standards







ASME A112.18.1/CSA B125.1

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	BAF	Brushed French Gold
	BN	Brushed Nickel
	SN	Polished Nickel


---

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

2-6-2025 21:22 - US



## Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.5 gal/min (5.7 l/min)

Drain included: Yes

Spout:

Spout reach: 4-7/8" (124 mm)

Handshower rated max flow: 1.5 gal/min (5.7 l/min)

## Notes

Install this product according to the installation instructions.