

KALLISTA®

Per Se® by KALLISTA
Single-control sink faucet, tall spout
P26624-00

Features

- High-quality solid-brass construction for durability and reliability
- Spout reach is 4-7/8" (124 mm)
- Spout height is 8-5/8" (219 mm)
- Includes metal pop-up drain with 1-1/4" metal tailpiece
- Single-hole installation
- 1.2 gpm (4.5 lpm) maximum flow rate
- A selection of products within this collection is in stock and ready to ship. Please visit kallista.com/readytoship for the complete list of Ready-to-Ship products and finishes



Recommended Products/Accessories

P24669-00 Towel ring
P34701-00 Towel Bar, 18"
P34702-00 Towel Bar, 12"
P34700-00 Towel Bar, 24"
P34708-00 Toilet Paper Holder
P34706-00 Hook



CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ICC/ANSI A117.1
CSA B651
OBC

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	French Gold
	BAF	Brushed French Gold
	BN	Brushed Nickel
	SN	Polished Nickel

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

2-15-2025 21:57 - US

KALLISTA

Per Se® by KALLISTA
Single-control sink faucet, tall spout
P26624-00



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 4-13/16" (123 mm)

Notes

OBC, CSA B651 compliant when installed to the specific requirements of these regulations.