KALLISTA.


Foundations by KALLISTA Thermostatic rough-in with volume control & stops

P29500-WS

Features

- Brass valve body
- One-piece diaphragm cartridge design for ease of maintenance
- Single-lever design cycles from off through cold to hot with integrated volume control
- Thermostatic technology automatically maintains outlet temperature during water pressure fluctuations and/or inlet water temperature changes
- Features a high-temperature-limit stop to help prevent scalding
- 9 gpm (34 l/min) maximum flow rate at 45 psi

Optional Products/Accessories K-10350 Deep rough-in kit K-10351 Test cap for K-8300 Series valve bodies




Codes/Standards ASME A112.18.1/CSA B125.1 ASSE 1016/ASME A112.1016/CSA B125.16

KALLISTA: Five-Year Limited Warranty See website for detailed warranty information.

KALLISTA.

Foundations by KALLISTA Thermostatic rough-in with volume control & stops

P29500-WS



Valve body: Machined-brass