

KALLISTA®


Bandeau™ by KALLISTA Rain Showerhead P30530-00

Features

- High-quality solid-brass construction for durability and reliability
- Optional Halo mount and Chandelier mount (sold separately)
- Must be mounted onto solid wood
- Maximum flow rate of 2.5 gpm (9.5 lpm)
- Single-function spray
- 16" oval
- Unlacquered Brass (ULB) available in North America and the United Kingdom only

Recommended Products/Accessories

P30531-00 Halo Extension Mount
P30514-00 Chandelier Mount
P24925-LV Thermostatic Trim, Lever Handle
P34132-LV Thermostatic trim, lever handle
P21383-LV Thermostatic trim, lever handle
P24421-LV Thermostatic trim, lever handle



Codes/Standards










ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	SN	Polished Nickel
	PGP	Polished Graphite
	BV	Brushed Bronze
	BN	Brushed Nickel
	BGP	Brushed Graphite
	BAF	Brushed French Gold

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to www.kallista.com.

6-11-2025 05:30 - US/CA

KALLISTA®

Bandeau™ by KALLISTA

Rain Showerhead
P30530-00



Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

Notes

For use with automatic compensating valves rated at 2.1 gal/min (7.9 l/min) or less.

Install this product according to the installation instructions.