


## Features

- High quality full brass construction for durability and reliability
- Optional Halo mount and Chandelier mount (sold separately)
- Must be mounted onto solid wood
- Maximum flow rate of 2.5 gpm (9.5 lpm)
- Single-function spray
- 16" oval
- Unlacquered Brass (ULB) available in North America and the United Kingdom only



## Recommended Products/Accessories

- P30531-00 Halo Extension Mount (Qty 2)
- P30514-00 Chandelier Mount (Qty 2)
- P24925-LV Thermostatic Trim, Lever Handle (Qty 2)
- P34132-LV Thermostatic trim, lever handle (Qty 2)
- P21383-LV Thermostatic trim, lever handle (Qty 2)
- P24421-LV Thermostatic trim, lever handle (Qty 2)

## Codes/Standards










- ASME A112.18.1/CSA B125.1
- DOE - Energy Policy Act 1992

## KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.


## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	BAF	Brushed French Gold
	SN	Polished Nickel
	PGP	Polished Graphite
	BV	Brushed Bronze
	BN	Brushed Nickel
	BGP	Brushed Graphite

# KALLISTA®

Bandeau™ by KALLISTA  
Rain Showerhead, White Carrara band  
P30530-WC



## Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

## Notes

For use with automatic compensating valves rated at 2.1 gal/min (7.9 l/min) or less.

Install this product according to the installation instructions.