KALLISTA

One™ by KALLISTA

Sink faucet, low spout, FP5 decorative handles

P32412-LV

Features

- Solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- Spout reach is 5-5/16" (135 mm)
- Laminar flow
- Includes soft-touch drain
- 1.2 gpm (4.5 lpm) maximum flow rate

Recommended Products/Accessories

P74234-WO Under-mount Sink, Soft Rectangle with Overflow, Glazed
P24492-CR Sink Faucet, Tall Spout, Cross Handles
P34401-00 Towel Bar, 24"
P34407-00 Disc Hook

ADA | CSA B651 | OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	BAF	Brushed French Gold
	BN	Brushed Nickel
	SN	Polished Nickel
	2MB	Brushed Moderne Brass
	BV	Brushed Bronze

KALLISTA

One™ by KALLISTA

Sink faucet, low spout, FP5 decorative handles

P32412-LV



Technical Information

All product dimensions are nominal.

Faucet flow rate:	1.5 gal/min (5.7 l/min)
Drain included:	Yes
Drain with overflow:	Yes

Spout:

Spout reach:	5-5/16" (135 mm)

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.