

# KALLISTA®

## Bezel™ by CRISTINA Rubinetterie Bezel™ Wall Mount Single Control Sink Faucet, White Carrara Handle P33166-WC

### Features

- High-quality solid-brass construction for durability and reliability
- Italian natural stone handle
- Faceted knob handle design with precision alignment
- Single-handle control
- Spout reach is 7-1/8" (181 mm)
- 1.2 gpm (4.5 lpm) maximum flow rate
- Includes quiet clicker drain
- Required rough-in sold separately

### Required Products/Accessories

For wall-mount installation

P32716-00 Wallmount Single Control Rough In


### Recommended Products/Accessories

P32742-00 Bezel™ 18" Towel Bar

P32744-00 Bezel™ 12" Towel Bar

P32745-00 Bezel™ Robe Hook

P32746-00 Bezel™ Toilet Paper Holder



### Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

DOE - Energy Policy Act 1992

EPA WaterSense®







California Energy Commission (CEC)

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty  
information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color   | Code | Description           |
|---|------|-----------------------|
|  | CP   | Polished Chrome       |
|  | BLH  | Blush Brass           |
|  | PGP  | Polished Graphite     |
|  | BN   | Brushed Nickel        |
|  | BGP  | Brushed Graphite      |
|  | 2MB  | Brushed Moderne Brass |

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

1-30-2025 12:25 - US/CA

# KALLISTA

## Bezel™ by CRISTINA Rubinetterie Bezel™ Wall Mount Single Control Sink Faucet, White Carrara Handle P33166-WC



### Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 7-1/8" (181 mm)

### Notes

Install this product according to the installation instructions.