

KALLISTA®

Bezel™ by CRISTINA Rubinetterie Bezel™ Wall Mount Widespread Sink Faucet, Guatemala Stone Handles P33168-GTM

Features

- High-quality solid-brass construction for durability and reliability
- Knob handles constructed of natural stone
- Faceted knob handle design with precision alignment
- Spout reach is 7-1/8" (181 mm)
- 1.2 gpm (4.5 lpm) maximum flow rate
- Includes quiet clicker drain
- Required rough-in sold separately

Required Products/Accessories

For wall-mount installation

P32717-00 Wallmount Widespread Rough In


Recommended Products/Accessories

P32742-00 Bezel™ 18" Towel Bar

P32744-00 Bezel™ 12" Towel Bar

P32745-00 Bezel™ Robe Hook

P32746-00 Bezel™ Toilet Paper Holder



Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

DOE - Energy Policy Act 1992

EPA WaterSense®







California Energy Commission (CEC)

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BLH	Blush Brass
	PGP	Polished Graphite
	BN	Brushed Nickel
	BGP	Brushed Graphite
	2MB	Brushed Moderne Brass

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

2-20-2025 22:41 - US/CA

KALLISTA

Bezel™ by CRISTINA Rubinetterie Bezel™ Wall Mount Widespread Sink Faucet, Guatemala Stone Handles P33168-GTM



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: $7\text{-}1/8"$ (181 mm)

Notes

Install this product according to the installation instructions.