

# KALLISTA®

## Bezel™ by CRISTINA Rubinetterie Bezel™ Floormount Single Control Sink Faucet, Guatemala Stone Handle P33170-GTM

### Features

- High-quality solid-brass construction for durability and reliability
- Knob handle constructed of natural stone
- Faceted knob handle design with precision alignment
- Single-handle control
- Floor-mount, single hole installation
- 41-3/8" (1051 mm) total height
- 37-13/16" (960 mm) spout height
- Spout reach is 7-5/16" (186 mm)
- 1.2 gpm (4.5 lpm) maximum flow rate
- Includes quiet clicker drain
- Required rough-in sold separately

### Required Products/Accessories

For freestanding installation

P32715-00 Floormount Rough In

### Recommended Products/Accessories

P32742-00 Bezel™ 18" Towel Bar

P32744-00 Bezel™ 12" Towel Bar

P32745-00 Bezel™ Robe Hook

P32746-00 Bezel™ Toilet Paper Holder



### Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

DOE - Energy Policy Act 1992

EPA WaterSense®







California Energy Commission (CEC)

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BLH	Blush Brass
	BN	Brushed Nickel
	BGP	Brushed Graphite
	2MB	Brushed Moderne Brass
	PGP	Polished Graphite

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

9-21-2025 11:21 - US/CA

# KALLISTA®

## Bezel™ by CRISTINA Rubinetterie Bezel™ Floormount Single Control Sink Faucet, Guatemala Stone Handle P33170-GTM



### Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 7-5/16" (186 mm)

### Notes

Install this product according to the installation instructions.