

KALLISTA®

002® by KALLISTA Single Control Sink Faucet, Tall Spout, Lever Handle P34121-00

Features

- High-quality metal construction for durability and reliability
- Single-hole installation
- 6-15/16" (176 mm) spout height
- Spout reach is 5-3/16" (132 mm)
- 8-5/8" (219 mm) total height
- 1.2 gpm (4.5 lpm) maximum flow rate
- Includes drain and lift rod
- Laminar flow

Recommended Products/Accessories

P34136-00 Towel Bar, 18"
P34137-00 Towel Bar, 24"
P34138-00 Towel Ring
P34139-00 002™ Hook
P34141-00 Toilet Paper Holder



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	2MB	Brushed Moderne Brass
	SN	Polished Nickel
	BN	Brushed Nickel
	BAF	Brushed French Gold

KALLISTA®

002® by KALLISTA Single Control Sink Faucet, Tall Spout, Lever Handle P34121-00



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with
overflow: Yes

Drain tailpiece
included: Yes

Spout:

Spout reach: 5-3/8" (136 mm)

Notes

Install this product according to the
installation instructions.

ADA, OBC, CSA B651 compliant when
installed to the specific requirements of
these regulations.