

# KALLISTA®

## 002® by KALLISTA Single Control Sink Faucet, Low Spout, Lever Handle P34122-00

### Features

- High-quality metal construction for durability and reliability
- Single-hole installation
- 4-11/16" (119 mm) spout height
- Spout reach is 5-5/16" (135 mm)
- 6-3/8" (162 mm) faucet height
- Includes drain and lift rod
- 1.2 gpm (4.5 lpm) maximum flow rate

### Recommended Products/Accessories

P34136-00 Towel Bar, 18"  
P34137-00 Towel Bar, 24"  
P34138-00 Towel Ring  
P34139-00 002™ Hook  
P34141-00 Toilet Paper Holder



ADA

CSA B651

OBC

### Codes/Standards

ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 61  
NSF/ANSI/CAN 372  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty  
information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color                                                                               | Code | Description           |
|-------------------------------------------------------------------------------------|------|-----------------------|
|  | CP   | Polished Chrome       |
|  | BL   | Matte Black           |
|  | BAF  | Brushed French Gold   |
|  | BN   | Brushed Nickel        |
|  | SN   | Polished Nickel       |
|  | 2MB  | Brushed Moderne Brass |

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

10-12-2025 19:41 - US/CA

# KALLISTA®

## 002® by KALLISTA Single Control Sink Faucet, Low Spout, Lever Handle P34122-00



### Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with  
overflow: Yes

Drain tailpiece  
included: Yes

### Spout:

Spout reach: 5-3/8" (136 mm)

### Notes

Install this product according to the  
installation instructions.

ADA, OBC, CSA B651 compliant when  
installed to the specific requirements of  
these regulations.