


KALLISTA®

Vice™ by KALLISTA Wall Mount Widespread Sink Faucet, Crank Handles P34865-CP

Features

- High-quality metal construction for durability and reliability
- 1.2 gpm (4.5 lpm) maximum flow rate
- Widespread sink faucet for 8" (203 mm) centers
- Includes soft-touch drain
- Laminar flow
- Required rough-in sold separately

Recommended Products/Accessories



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

OBC

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

10-17-2025 10:30 - US/CA

KALLISTA®

Vice™ by KALLISTA Wall Mount Widespread Sink Faucet, Crank Handles P34865-CP



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with
overflow: Yes

Drain tailpiece
included: Yes

Spout:

Spout reach: 8-15/16" (227 mm)

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.