


KALLISTA®

Vice™ by KALLISTA Widespread Sink Faucet, Wheel Handles P34884-BN

Features

- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- 1.2 gpm (4.5 lpm) maximum flow rate
- Includes soft-touch drain
- Laminar flow



Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

KALLISTA® Five-Year Limited Warranty


See website for detailed warranty
information.

KALLISTA

Vice™ by KALLISTA

Widespread Sink Faucet, Wheel Handles

P34884-BN



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with
overflow: Yes

Drain tailpiece
included: Yes

Spout:

Spout reach: 6-7/8" (175 mm)

Notes

Install this product according to the
installation instructions.

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

10-14-2025 15:15 - US/CA