KALLISTA

Vice™ by KALLISTA
Wall Mount Widespread Sink Faucet, Wheel Handles
P34885-BN

Features
- High-quality metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- 1.2 gpm (4.5 lpm) maximum flow rate
- Includes soft-touch drain
- Laminar flow
- Required rough-in sold separately



Required Products/Accessories
For wall-mount installation
P29304-00 Rough-In

Recommended Products/Accessories
P34595-CP Towel Bar, 24"
P34586-CP Freestanding Bath Faucet, Less Handshower
P34596-CP Towel Ring

Codes/Standards
ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

KALLISTA® Five-Year Limited Warranty
See website for detailed warranty information.

Available Colors/Finishes
Color tiles intended for reference only.

Color	Code	Description
	BGP	Brushed Graphite
	SN	Polished Nickel

KALLISTA

Vice™ by KALLISTA

Wall Mount Widespread Sink Faucet, Wheel Handles

P34885-BN



Technical Information

All product dimensions are nominal.

Faucet flow rate:	1.2 gal/min (4.5 l/min)
Drain included:	Yes
Drain with overflow:	Yes
Drain tailpiece included:	Yes

Spout:

Spout reach:	8-15/16" (227 mm)

Notes

Install this product according to the installation instructions.