

KALLISTA®

Foundations by KALLISTA Air-Induction Medium Contemporary Rain Showerhead Eco P38540-G

Features

- High quality full brass construction for durability and reliability
- Required shower arm sold separately
- 1.75 gpm (6.6 lpm) maximum flow rate
- Includes escutcheon
- Single-function spray
- Diameter is 10" (254 mm)

Required Products/Accessories

P21520-00 Rain Showerhead Arm

or


P21521-00 Rain Showerhead Arm

or

P21522-00 12" ceiling-mount rain showerhead arm

or

P21523-00 Wall-Mount Rain Showerhead Arm



Codes/Standards

ASME A112.18.1/CSA B125.1

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	AF	French Gold
	BN	Brushed Nickel
	BAF	Brushed French Gold
	PGP	Polished Graphite
	BV	Brushed Bronze
	SN	Polished Nickel
	BGP	Brushed Graphite
	2MB	Brushed Moderne Brass

1-888-4-KALLISTA (1-888-452-5547)



Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

2-24-2026 04:00 - US/CA

KALLISTA®

Foundations by KALLISTA Air-Induction Medium Contemporary Rain Showerhead Eco P38540-G



Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

Notes

For use with automatic compensating valves rated at 1.4 gal/min (5.3 l/min) or less.

Install this product according to the installation guide.