

Traditional Round Rainhead

Product Description: Traditional Round Rainhead

Product Code: 13692D-CP, 13693D-CP
13694D-CP

Product Dimensions: 8" - Ø214 mm x H95 mm
10" - Ø265 mm x H95 mm
12" - Ø316 mm x H95 mm

Colour/Finish: Polished Chrome

Material: Brass

Recommended Pressure (bar): 0.1

Product Weight (kg): 2.17 (13692D-CP)
3.31 (13693D-CP)
4.26 (13694D-CP)

Fixings Included: Yes

Guarantee (Years): 5

Additional Information: Superior spray performance with Katalyst + Spray technology, delivers a luxurious and drenching 'rain' experience. Masterclean™ spray face with translucent nozzles for ease of cleaning.

Requires: Kohler Ceiling Arm E10043-CP or Kohler Wall Arm 1190093-CP



13692D-CP - 8" (78 Nozzles)



13693D-CP - 10" (78 Nozzles)



13694D-CP - 12" (102 Nozzles)

Notes:

Kohler UK


Sales Tel: +44 (0) 844 571 0048 Fax: +44 (0) 844 571 1001
Technical Tel: +44 (0) 151 606 5034 Fax: +44 (0) 151 638 0303
www.kohler.co.uk

THE BOLD LOOK
OF **KOHLER**®


Traditional Round Rainheads

Dimensions (mm)


13692D-CP - 8"



13693D-CP - 10"



13694D-CP - 12"



Kohler UK

Sales Tel: +44 (0) 844 571 0048 Fax: +44 (0) 844 571 1001

Technical Tel: +44 (0) 151 606 5034 Fax: +44 (0) 151 638 0303

www.kohler.co.ukTHE BOLD LOOK
OF **KOHLER**®