

KALLISTA®

Obidos
Decorative Vessel
P72061-00

Features

- Constructed of cast bronze
- 15-3/4" (400 mm) total width
- 10-7/8" (276 mm) total length
- 4-1/2" (114 mm) depth
- Recommended pairing with KALLISTA wall-mounted or vessel-height single control faucets

Recommended Products/Accessories

P21223-LV
P31424-00
P30800-00
P21642-00 Supply Valve

Codes/Standards



None Applicable

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	TBR	Traditional Bronze
	WHB	White Satin Bronze

Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Vessel

Bowl area (Center): Length: 14-3/4" (375 mm)
Width: 10-1/8" (257 mm)
Bowl depth: 4" (102 mm)
Water depth: 4" (102 mm)

Notes

Install this product according to the installation instructions.