

KALLISTA®

Under-mount Sink, Centric Oval with Overflow, Glazed
P74232-WO

Perfect

Features

- Constructed of Vitreous China
- 19-1/8" (486 mm) total width
- 15-15/16" (405 mm) total length
- 6-5/8" (168 mm) total depth
- Includes mounting hardware
- Built-in overflow
- ADA compliant
- Glazed underside

Recommended Products/Accessories

P23202-LV
P24492-LV
P21688-00 Bottle Trap
P21644-00 Valve Shroud

ADA

Codes/Standards

ASME A112.19.2/CSA B45.1

ADA

ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

KALLISTA[®] Under-mount Sink, Centric Oval with Overflow, Glazed

Perfect
P74232-WO

Technical Information

All product dimensions are nominal.

Bowl configuration:	Single
Installation:	Undermount
Bowl area:	Length: 17" (432 mm) Width: 14" (356 mm) Bowl depth: 6-5/8" (168 mm) Water depth: 3-5/8" (92 mm)
Drain hole:	1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.