

KALLISTA®

Perfect
Under-mount Sink, Soft Oval with Overflow, Glazed
P74241-WO

Features

- Ready-to-Ship (RTS) Program, in-stock and ready for immediate shipment
- Constructed of Vitreous China
- 19-1/8" (486 mm) total width
- 15-15/16" (405 mm) total length
- 7-3/4" (197 mm) total depth
- Includes mounting hardware
- Built-in overflow
- ADA compliant
- Glazed underside

ADA

Codes/Standards

ASME A112.19.2/CSA B45.1

ADA

ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Recommended Products/Accessories

P25006-LV

P24601-CR

P21641-00

P21644-00 Valve Shroud

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

2-27-2022 03:14 - US

KALLISTA®

Perfect
Under-mount Sink, Soft Oval with Overflow, Glazed
P74241-WO

Technical Information

All product dimensions are nominal.

Bowl configuration:	Single
Installation:	Undermount
Bowl area:	Length: 17-1/8" (435 mm) Width: 13-15/16" (354 mm) Bowl depth: 7-3/4" (197 mm) Water depth: 4-9/16" (116 mm)
Drain hole:	1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.