

Features

- Three-way mitered joinery on vanity frame
- Mitered thin frame drawer detail
- Top drawers are plumbing drawers
- Bottom drawers are plumbing drawers
- Open shelf storage
- Removable glass drawer dividers included

Materials & Construction


- Solid wood and veneer construction
- Full plywood back panel, no cutout
- Dovetailed drawers
- Pre-installed solid stainless steel hardware
- Blum undermount full extension slow close slides
- Durable, moisture resistant polyurethane finish
- Adjustable leveling feet

Options

- Available in:
CVSK6020469, Rustic Oak paired with Brushed Pewter
- Coordinating mineral cast sink with drain cover, TA60MDO___ - 8CS9
- Coordinating mirrors available
- Coordinating linen cabinet available

Dimensions

Width: 59-5/8"
Height: 28-1/8"
Depth: 22-3/4"



Model Number Key

PRODUCT LINE	CATEGORY	COLLECTION	WIDTH	FINISH OPTIONS	OPTIONS
C = Craft Series	V = Vanity	SK = Skaarsgard	60"	(See above)	(See above)

Skaarsgard 60" Vanity CVSK60

