

### Features

- Acrylic and reinforced with fiberglass
- Drop-in
- Includes pillow head
- Includes pop-up drain and overflow
- 1800 x 800 x 550 mm


### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- IAPMO/UPC
- TIS 2141-2546

### Installation Notes

Install this product according to the installation guide. Floor support under bath must provide for a minimum of 374 kg/square meter loading.



### Technical Information


Fixture:	
Basin area:	
Basin area bottom	1122 x 503 mm
Basin area top	1635 x 680 mm
*Approximate measurements for comparison only.	

To overflow:	
Water depth	393 mm
Capacity	271 liters
Drain hole	ø38 mm (1-1/2")
Overflow hole	ø52 mm
Weight	28 kg

### Specified Model

Model	Description	Color/Finishes
K-1704X-1P	Evok plain bath with orange pillow	0: White
K-1704X-BFH1	Evok 1.8 M Bathtub/Faucet holes 72292T-4	0: White

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)  
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

### Product Diagram

## อ่างอาบน้ำ K-1704X

### คุณลักษณะ


- อะครีลิกเสริมใยแก้ว
- แบบฝัง
- พร้อมหมอนรองศีรษะ
- พร้อมสะดืออ่างแบบปี๊ปอปฟ์และท่อน้ำล้น
- 1800 x 800 x 550 มม.

### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI Z124.1.2
- IAPMO/UPC
- มอก. 2141-2546

### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง  
พื้นที่ใช้รองรับอ่างอาบน้ำต้องสามารถรับน้ำหนักอย่างน้อย 374 กก./ตร.ม.



### ข้อมูลเฉพาะ

ผลิตภัณฑ์:	
พื้นที่อ่างอาบน้ำ:	
พื้นที่ด้านล่าง	1122 x 503 มม.
พื้นที่ด้านบน	1635 x 680 มม.
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น	


ระดับน้ำล้น:	
ระดับน้ำล้น	393 มม.
ความจุน้ำ	271 ลิตร
รูท่อน้ำทิ้ง	Ø38 มม. (1-1/2")
รูท่อน้ำล้น	Ø52 มม.
น้ำหนัก	28 กิโลกรัม

### รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-1704X-1P	อ่างอาบน้ำพร้อมหมอนรองศีรษะสีส้ม รุ่น อีโวก 1800	0: สีขาว
K-1704X-BFH1	อ่างอาบน้ำแบบมีรูท่อน้ำ 72292T-4 รุ่น อีโวก 1800	0: สีขาว

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)  
หน่วย: มม.

K-1704X-1P



K-1704X-BFH1



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

### ภาพแสดงผลิตภัณฑ์