

Features

- Brass construction
- Single-hole mounting
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- Flexible connections for easy installation
- Includes pop-up drain with lift rod and tailpiece
- 89 mm spout reach
- Lever handle

TALL SINGLE-HOLE SINGLE CONTROL
LAVATORY FAUCET
K-19774X



Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552

Colors/Finishes

- CP: Polished Chrome

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-19774X	Symbol single-hole single control lavatory faucet	CP

Product Specification:


The tall single-hole single control lavatory faucet shall be made of brass construction. Product shall feature a one-piece, self-contained ceramic disc valve, allowing volume and temperature control. Product shall be for single-hole mounting. Product shall feature a 89 mm spout reach, lever handle, a pop-up drain with lift rod and tailpiece, and flexible connections for easy installation. Faucet shall be Kohler Model K-19774X-CP.

SYMBOL

Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.
Unit: mm.



Product Diagram

SYMBOL TALL SINGLE-HOLE SINGLE CONTROL LAVATORY FAUCET
Page 2/4
1046768-X4-A

KOHLER®

คุณลักษณะ

- ผลิตจากทองเหลือง
- ติดตั้งแบบรูก๊อกเดี่ยว
- เซรามิควาล์ว วาล์วก๊อกน้ำเดี่ยวควบคุมทั้งปริมาณน้ำและอุณหภูมิ
- ติดตั้งด้วยสายน้ำดี ทำให้ติดตั้งได้ง่าย
- พร้อมสະดืออ่างแบบป๊อบอัพ
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 89 มม.
- มือบิดแบบก้านโยก

ก๊อกผสมอ่างล้างหน้าทรงสูง
แบบก้านโยก

K-19774X



มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2067-2552

สี/วัสดุเคลือบผิว

- CP: สีโครมเงา

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-19774X	ก๊อกผสมอ่างล้างหน้าทรงสูงแบบก้านโยก รุ่น ชิมโบล	CP

ข้อมูลผลิตภัณฑ์:

ก๊อกผสมอ่างล้างหน้าผลิตจากทองเหลือง วาล์วก๊อกน้ำเป็นเซรามิควาล์ว ก๊อกน้ำวาล์วเดี่ยวที่ควบคุมทั้งปริมาณน้ำและอุณหภูมิ ก๊อกน้ำติดตั้งแบบรูก๊อกเดี่ยว มีระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 89 มม. ก๊อกน้ำแบบก้านโยกพร้อมสະดืออ่างแบบป๊อบอัพ ติดตั้งด้วยสายน้ำดี ทำให้ติดตั้งได้ง่าย ก๊อกน้ำรุ่นนี้คือ ก๊อกน้ำโครห์เลอร์รุ่น K-19774X-CP


ซิมโบล

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์

ก๊อกผสมอ่างล้างหน้าทรงสูงแบบก้านโยก รุ่น ซิมโบล

หน้า 4/4

1046768-X4-A

KOHLER®