

KITCHEN SINK K-3674X

Features

- 304 stainless steel
- Self-rimming
- Includes S-trap, overflow trap, quick flow strainers and installation hardware
- Exceptional sound-absorption technology (SilentShield technology)
- 476 mm diameter


Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI A112.19.3M/CSA B45.4

Installation Notes

Install this product according to the installation guide.



Technical Information

Fixture:	
Basin area	451 mm
Water depth	152 mm
Drain hole	38 or 51 mm (1-1/2" or 2")
*Approximate measurements for comparison only.	

Included components:	
S-trap	1200370
Strainer	5163T-NA
Template	1119905-X7


Specified Model

Model	Description	Color/Finished	
K-3674X-F	Brinx stainless steel sink	NA: None Applicable	

Recommended Accessories			
K-668X	Candide kitchen faucet	CP: Polished Chrome	
K-45406X-4	Cuff kitchen faucet	CP: Polished Chrome	
K-15609X-4	Elate kitchen faucet	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> BN: Vibrant Brushed Nickel

Dimensions are approximate.

Unit: mm



Product Diagram

อ่างล้างจาน K-3674X

คุณลักษณะ


- ผลิตจากสแตนเลส สตีล เกรด 304
- แบบฝังบนเคาน์เตอร์
- พร้อมข้อต่อน้ำทิ้งแบบลงพื้น, ท่อน้ำล้นในตัว, สะดืออ่างแบบควิกไฟว์ และอุปกรณ์ติดตั้ง
- เทคโนโลยีโซเลนซิดด์ ช่วยลดการเกิดเสียงจากงานขาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- เส้นผ่าศูนย์กลาง 476 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI A112.19.3M/CSA B45.4

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง



ข้อมูลเฉพาะ


ผลิตภัณฑ์:	
พื้นที่อ่าง	451 มม.
ระยะน้ำลึก	152 มม.
ขนาดรูท่อน้ำทิ้ง	38 หรือ 51 มม. (1-1/2" หรือ 2")
*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น	

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้งแบบลงพื้น	1200370
สะดืออ่าง	5163T-NA
กระดาษแม่แบบ	1119905-X7

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3674X-F	อ่างล้างจานสแตนเลส รุ่นบริงซ์	NA: ไม่ระบุ
แนะนำให้ใช้ร่วมกับผลิตภัณฑ์		
K-668X	ก๊อกผสมอ่างล้างจาน รุ่นแคนดิด	CP: สีโครมเงา
K-45406X-4	ก๊อกผสมอ่างล้างจาน รุ่นคัพ	CP: สีโครมเงา
K-15609X-4	ก๊อกผสมอ่างล้างจาน รุ่นอีเลท	<input type="checkbox"/> CP: สีโครมเงา <input type="checkbox"/> BN: สีนิกเกิลปิดลาย

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์