


Features

- Multiple laminated glass designs and CleanCoat
- 8 mm thick tempered glass
- Tempered glass ensures maximum safety and durability
- Hinged passed test open-close at 200,000 times
- 30-degree hinge automatic homing feature.
- Frameless glass shower enclosure
- Stainless steel handle modern style, anti-corrosion and rusty
- Can open the door inside and outside, two-way choices and meet different space.
- Can choose to open the door (left or right hand door open for K-36950T only)
- Can be customized non standard (For K-36950T only)

L-SHAPE HINGED ONE DOOR

K-36950X ALSO K-36950T



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z97.1
- ASTM B221-00
- BS EN 12150-2
- BS EN 14428
- GB 5237.2
- GB 15763.2
- QB 2584

Glass Options

- C: Clean Coat
- L: Clear
- L3: Tangle
- L4: Intrex
- L5: Lake Mist

Frame and Accessory Finishes/Colors:

- 0: White
- SHP: Polished Silver
- LN: Cool Grey

Specified Model

Model	Description	Glass Options					Frame Finishes/Colors
K-36950X-C	Singulier hinged one door, L-shape, 2-panels with clean coat						
K-36950T	Singulier hinged one door, L-shape, 2-panels	<input type="checkbox"/> C	<input type="checkbox"/> L	<input type="checkbox"/> L3	<input type="checkbox"/> L4	<input type="checkbox"/> L5	<input type="checkbox"/> SHP

Recommended Accessories			
K-17232X	Shower Tower, height 1830 mm	<input type="checkbox"/> 0	
K-17233X	Shower Tower, height 1000 mm	<input type="checkbox"/> 0	

Product Specification:

Pivot shower door shall have 8 mm thick tempered glass and multiple laminate glass designs and CleanCoat. Product shall have tempered glass ensures maximum safety and durability. Product shall have hinges passed test open-close at 200,000 times. Product shall have 30-degree hinge automatic homing feature. Product can open the door inside and outside, two-way choices and meet different space. Product shall include stainless steel handle modern style, anti-corrosion and rusty. Product can choose to open the door (left or right hand door open for K-36950T only). Product can be customized non standard (For K-36950T only). Product shall be Kohler Model K-____-____-_____.

SINGULIER

Recommended Accessories			
K-37069X	Shower divider, square, contemporary, 900 x 900 x 60 mm	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37070X	Shower divider, square, contemporary, 1000 x 1000 x 60 mm	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37071X	Shower divider, square, contemporary, 1200 x 1200 x 60 mm	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37081X	Shower divider, square, classic, 900 x 900 x 100 mm	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37082X	Shower divider, square, classic, 1000 x 1000 x 100 mm	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37083X	Shower divider, square, classic, 1200 x 1200 x 100 mm	<input type="checkbox"/> 0	<input type="checkbox"/> LN


Technical Information

Fixture:	
Weight	71.5 kg

Dimensions are approximate.
Unit: mm.

Installation Notes

Install this product according to the installation guide.
Width more than 1500 mm the fixed glass need to add glass support rod.




Model	A	B	C	D (Walk Through)
K-36950X	1900	1100	1000	643
K-36950T	1850-2000	900-1200	700-1200	470-670

Product Diagram

คุณลักษณะ

- กระจกลามิเนตเคลือบผิวกระจกหลายชั้นด้วยระบบ เคลือบโคท (CleanCoat)
- กระจกเทมเปอร์หนา 8 มม.
- กระจกเทมเปอร์ให้ความปลอดภัยและความทนทาน
- บานพับผ่านการทดสอบการเปิด-ปิด เสมือนการใช้งานจริง 200,000 ครั้ง
- บานพับปิดอัตโนมัติ แบบ 30 องศา
- ฉากกันน้ำจากกระจกบานเปลือย
- มือจับทำจากสแตนเลสช่วยป้องกันสนิมและการกัดกร่อน
- สามารถเปิดได้สองทิศทาง ทั้งด้านในและด้านนอก
- สามารถเลือกทิศทางในการเปิดประตูได้ (ด้านซ้ายหรือด้านขวา สำหรับรุ่น K-36950T เท่านั้น)
- สามารถปรับขนาดได้นอกเหนือจากมาตรฐาน (สำหรับรุ่น K-36950T เท่านั้น)

ตู้อาบน้ำบานเปลือยแบบบานพับรูปตัวแอล K-36950X และ K-36950T



มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ANSI Z97.1
- ASTM B221-00
- BS EN 12150-2
- BS EN 14428
- GB 5237.2
- GB 15763.2
- QB 2584

ชนิดกระจก

- C: เคลือบโคท
- L: กระจกใส
- L3: ลายแพงเกิด
- L4: อิมเทรก
- L5: ลายหมอก

สี/วัสดุเคลือบผิว

- 0: สีขาว
- SHP: สีเงิน
- LN: สีเทา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	ชนิดกระจก	สี/วัสดุเคลือบผิว
K-36950X-C	ตู้อาบน้ำบานเปลือยแบบบานพับรูปตัวแอล 1 บานเปิด 2 บาน ถาวรพร้อมกระจกเคลือบผิวเคลือบโคท รุ่น ซิงกูลิเย่		<input type="checkbox"/> SHP
K-36950T	ตู้อาบน้ำบานเปลือยแบบบานพับรูปตัวแอล 1 บานเปิด 2 บาน รุ่น ซิงกูลิเย่	<input type="checkbox"/> C <input type="checkbox"/> L <input type="checkbox"/> L3 <input type="checkbox"/> L4 <input type="checkbox"/> L5	<input type="checkbox"/> SHP

ข้อมูลผลิตภัณฑ์:

ฉากกันน้ำแบบเปิดผลิตจากกระจกลามิเนตเคลือบผิวกระจกหลายชั้นด้วยระบบเคลือบโคท (CleanCoat) ผลิตภัณฑ์มีขนาดกระจกเทมเปอร์หนา 8 มม. ผลิตภัณฑ์มีกระจกเทมเปอร์ให้ความปลอดภัยและความทนทาน ผลิตภัณฑ์มีบานพับผ่านการทดสอบการเปิด-ปิด เสมือนการใช้งานจริง 200,000 ครั้ง ผลิตภัณฑ์มีบานพับปิดอัตโนมัติแบบ 30 องศา ผลิตภัณฑ์มีฉากกันน้ำจากกระจกบานเปลือย ผลิตภัณฑ์มีมือจับทำจากสแตนเลสช่วยป้องกันสนิมและการกัดกร่อน ผลิตภัณฑ์สามารถเปิดได้สองทิศทาง ทั้งด้านในและด้านนอก ผลิตภัณฑ์สามารถเลือกทิศทางในการเปิดประตูได้ (ด้านซ้ายหรือด้านขวา สำหรับรุ่น K-36950T เท่านั้น) ผลิตภัณฑ์สามารถปรับขนาดได้นอกเหนือจากขนาดมาตรฐาน (สำหรับรุ่น K-36950T เท่านั้น) ผลิตภัณฑ์รุ่นนี้คือ ผลิตภัณฑ์โคห์เลอร์รุ่น K-_____ - _____ - _____.

ซิงกูลิเย่

อุปกรณ์แนะนำ			
K-17232X	ชั้นวางของ ความสูง 1830 มม.	<input type="checkbox"/> 0	
K-17233X	ชั้นวางของ ความสูง 1000 มม.	<input type="checkbox"/> 0	
K-37069X	ธรณีประตู แบบตรง คอนเทมโพรารี ขนาด 900 x 900 x 60 มม.	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37070X	ธรณีประตู แบบตรง คอนเทมโพรารี ขนาด 1000 x 1000 x 60 มม.	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37071X	ธรณีประตู แบบตรง คอนเทมโพรารี ขนาด 1200 x 1200 x 60 มม.	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37081X	ธรณีประตู แบบตรง คลาสสิก ขนาด 900 x 900 x 100 มม.	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37082X	ธรณีประตู แบบตรง คลาสสิก ขนาด 1000 x 1000 x 100 มม.	<input type="checkbox"/> 0	<input type="checkbox"/> LN
K-37083X	ธรณีประตู แบบตรง คลาสสิก ขนาด 1200 x 1200 x 100 มม.	<input type="checkbox"/> 0	<input type="checkbox"/> LN


ข้อมูลเฉพาะ

ผลิตภัณฑ์*:	
น้ำหนัก	73 กิโลกรัม

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุญญากาศโดยใช้คู่มือข้อแนะนำการติดตั้ง หากกระจกมีขนาดความกว้างมากกว่า 1500 มม. ต้องใช้ก้านแขวน

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



รุ่น	A	B	C	D (ประตูทางเข้า)
K-36950X	1900	1100	1000	643
K-36950T	1850-2000	900-1200	700-1200	470-670

ภาพแสดงผลิตภัณฑ์