

### KITCHEN SINK K-3748X

#### Features

- 304 stainless steel
- Self-rimming and undercounter
- Large and medium basin
- Includes flexible trap, overflow trap, quick flow strainers, cutting board, colander and installation hardware
- Exceptional sound-absorption technology (SilentShield technology)
- 860 x 480 x 210 mm


#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB/T 18884.2-2002

#### Installation Notes

Install this product according to the installation guide. Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.



#### Technical Information


Fixture:	Left bowl	Right bowl
Basin area	440 x 433 mm	300 x 433 mm
Water depth	160 mm	200 mm
Drain hole	ø90 mm	
Faucet hole	ø35 mm	
*Approximate measurements for comparison only.		

Included components:	
Flexible trap	SP1200369
Strainer	5163X-NA, SP1174273
Fixing clips	SP1127254
Cutting Board	SP1154975
Drain Board	SP1097089-U-NA/SP1097090-U-NA
Template	1117445-X7

#### Specified Model

Model	Description	Color/Finished
K-3748X-1F	Geog stainless steel sink	NA: None Applicable
Recommended Accessories		
K-6332X-4	Evoke pullout spray kitchen faucet	CP: Polished Chrome

Dimensions are approximate.  
Unit: mm



#### Product Diagram

### อ่างล้างจาน K-3748X

#### คุณลักษณะ


- ผลิตจากสแตนเลส สตีล เกรด 304
- แบบฝังบนเคาน์เตอร์และแบบฝังใต้เคาน์เตอร์
- หนึ่งหลุมครึ่ง
- พร้อมข้อต่อน้ำทิ้ง, ท่อน้ำล้น, สะตืออ่างแบบคูวิกไฟว์, เชียงไม้, ถาดเตรียมอาหาร, และอุปกรณ์ติดตั้ง
- เทคโนโลยีไฮเดรนซิลด์ ช่วยลดการเกิดเสียงจากจานชาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 860 x 480 x 210 มม.

#### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- GB/T 18884.2-2002

#### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง  
 เมื่อพื้นที่ว่างรอบขอบอ่างล้างจานไว้อย่างน้อย 2 นิ้ว (51 มม.)  
 สำหรับการติดตั้งอุปกรณ์ยึดอ่างล้างจานที่มาพร้อมกับผลิตภัณฑ์



#### ข้อมูลเฉพาะ


ผลิตภัณฑ์:	หลุมซ้าย	หลุมขวา
พื้นที่อ่าง	440 x 433 มม.	300 x 433 มม.
ระยะน้ำล้น	160 มม.	200 มม.
ขนาดรูท่อน้ำทิ้ง	Ø90 มม.	
ขนาดรูท่อน้ำ	Ø35 มม.	
*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น		

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้ง	SP1200369
สะตืออ่าง	5163X-NA, SP1174273
อุปกรณ์ติดตั้ง	SP1127254
เชียงไม้	SP1154975
ถาดเตรียมอาหาร	SPF1097089-U-NA/ SPF1097090-U-NA
กระดาษแม่แบบ	1117445-X7

#### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3748X-1F	อ่างล้างจานสแตนเลส หนึ่งหลุมครึ่ง รุ่นจ๊อบออกซ์	NA: สีตามวัสดุ
อุปกรณ์แนะนำ		
K-6332X-4	ก๊อกลมอ่างล้างจานชนิดฝักบัว รุ่นอีโวก	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ  
 หน่วย: มม.



ภาพแสดงผลิตภัณฑ์