

### EXPOSED WALL-MOUNT SHOWER MIXER K-45533X

#### Features

- Brass construction
- G1/2" connection
- Includes handshower with 1.5m hose
- Lever handle

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552


#### Installation Notes

Install this product according to the installation guide.




#### Specified Model

Model	Description	Color/Finished
K-45533X-4	Cuff exposed wall-mount shower mixer	CP: Polished Chrome



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.  
Unit: mm



Product Diagram

### คุณลักษณะ

- ผลิตจากทองเหลือง
- เกลียวข้อต่อ G1/2"
- พร้อมหัวฝักบัวสายอ่อนและสายยาว 1.5 เมตร
- มือบิดแบบก้านโยก

### มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552

### ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

## ก๊อกผสมยืนอาบแบบติดผนัง พร้อมฝักบัวสายอ่อน K-45533X



### รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-45533X-4	ก๊อกผสมยืนอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นคัพ	CP: สีโครมเงา



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์