


Features

- CleanCoat glass coating for easy glass care and maintenance
- 6 mm thick tempered glass
- Tempered glass ensures maximum safety and durability
- Aluminum frame coat by anodizing process
- Stainless steel hardware prevents rusting and corrosion
- Nylon coated rail and sliding door rollers prevents rusting, chlorine stains and easy for cleaning
- Assembled in package easily for installation
- 900 x 900 x 1850 mm
or 1000 x 1000 x 1900 mm (only for K-98641X)

ROUND CONER SLIDE DOOR

K-17116T

ALSO K-17116X/K-98641X



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z97.1
- ASTM B221-00
- BS EN 12150-2
- BS EN 14428
- GB 5237.2
- GB 15763.2
- QB 2584

Glass Options

- C: Clean Coat
- L: Clear

Frame/Colors:

- 0: White
- SHP: Polished Silver

Accessory Finishes/Colors:

- 0: White

Specified Model

Model	Description	Glass Options		Frame Finishes/Colors	
K-17116T	Nateo sliding shower door, round corner 900 x 900	<input type="checkbox"/> C	<input type="checkbox"/> L	<input type="checkbox"/> 0	<input type="checkbox"/> SHP
K-17116X	Nateo sliding shower door, round corner 900 x 900	<input type="checkbox"/> C		<input type="checkbox"/> 0	
K-98641X	Nateo sliding shower door, round corner 1000 x 1000	<input type="checkbox"/> C		<input type="checkbox"/> 0	

Recommended Accessories

K-1094X	Curved shower receptor (with drain) 1000 x 1000	<input type="checkbox"/> 0	
K-17226X-DR	Curved shower receptor (with drain) 900 x 900	<input type="checkbox"/> 0	
K-17232X	Shower tower, height 1830 mm	<input type="checkbox"/> 0	
K-17233X	Shower tower, height 1000 mm	<input type="checkbox"/> 0	

Product Specification:

The sliding shower door shall be made of tempered glass to ensure maximum safety and durability. Product shall be 6 mm thick tempered glass. Product shall have CleanCoat glass coating for easy glass care and maintenance. Product shall have aluminum frame coat by power coating process. Product shall be stainless steel hardware prevents rusting and corrosion. Product shall be nylon coated rail and sliding door rollers prevents rusting, chlorine stains and easy for cleaning. Product shall be assembled in package easily for installation. Product shall be Kohler Model K-_____-_____-_____.

NATEO

Technical Information

Fixture	Weight
K-17116T/K-17116X	35 kg
K-98641X	50 kg




Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.
Unit: mm

Model	A	B
K-17116T-**	1850 mm	872±7 mm
K-17116X-**		
K-98641X-**	1900 mm	972±7 mm

Note: Max door opening 460 mm



Product Diagram

คุณลักษณะ

- เคลือบผิวกระจกด้วยระบบเคลือบโคท (CleanCoat) ดูแลรักษาและทำความสะอาดได้ง่าย
- กระจกเทมเปอร์หนา 6 มม.
- กระจกเทมเปอร์ให้ความปลอดภัยและความทนทาน
- เฟรมอลูมิเนียมพ่นเคลือบสีขาวด้วยระบบ พาวเดอร์ โคท
- อุปกรณ์ติดตั้งทำจากสแตนเลส สตีล เพื่อป้องกันสนิม
- รางเลื่อนและล้อทำจากไนลอน เพื่อป้องกันสนิมหรือคราบจากคลอรีน และทำความสะอาดได้ง่าย
- ติดตั้งง่าย เนื่องจากประกอบชิ้นส่วนสำคัญให้ก่อนการจัดส่ง
- 900 x 900 x 1850 มม. หรือ 1000 x 1000 x 1900 มม. (สำหรับรุ่น K-98641X เท่านั้น)

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ANSI Z97.1
- ASTM B221-00
- BS EN 12150-2
- BS EN 14428
- GB 5237.2
- GB 15763.2
- QB 2584

รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	ชนิดกระจก		สีของกรอบ	
K-17116T	ตู้อบน้ำบานเลื่อนแบบโค้ง รุ่น โอดีออน 900 x 900	<input type="checkbox"/> C	<input type="checkbox"/> L	<input type="checkbox"/> 0	<input type="checkbox"/> SHP
K-17116X	ตู้อบน้ำบานเลื่อนแบบโค้ง รุ่น โอดีออน 900 x 900	<input type="checkbox"/> C		<input type="checkbox"/> 0	
K-98641X	ตู้อบน้ำบานเลื่อนแบบโค้ง รุ่น โอดีออน 1000 x 1000	<input type="checkbox"/> C		<input type="checkbox"/> 0	

อุปกรณ์แนะนำ			
K-1094X	ถาดรองอาบน้ำแบบโค้ง (พร้อมสะดือน้ำทิ้ง) 1000 x 1000	<input type="checkbox"/> 0	
K-17226X-DR	ถาดรองอาบน้ำแบบโค้ง (พร้อมสะดือน้ำทิ้ง) 900 x 900	<input type="checkbox"/> 0	
K-17232X	ชั้นวางของความสูง 1830 มม.	<input type="checkbox"/> 0	
K-17233X	ชั้นวางของความสูง 1000 มม.	<input type="checkbox"/> 0	

ข้อมูลผลิตภัณฑ์:

ตู้อบน้ำบานเลื่อนผลิตจากกระจกเทมเปอร์หนา 6 มม. ช่วยเพิ่มความปลอดภัยและความทนทาน ผิวกระจกเคลือบด้วยระบบเคลือบโคท (CleanCoat) เพื่อดูแลรักษาและทำความสะอาดได้ง่าย เฟรมอลูมิเนียมพ่นเคลือบสีขาวด้วยระบบ พาวเดอร์ โคท อุปกรณ์ติดตั้งทำจากสแตนเลส สตีล เพื่อป้องกันสนิม ส่วนรางเลื่อนและล้อทำจากไนลอน เพื่อป้องกันสนิมหรือคราบจากคลอรีน ทำความสะอาดได้ง่าย ผลิตภัณฑ์ติดตั้งง่ายเนื่องจากประกอบชิ้นส่วนสำคัญก่อนการจัดส่ง ผลิตภัณฑ์รุ่นนี้คือ ผลิตภัณฑ์โคห์เลอร์รุ่น K-____-____-____.

ตู้อบน้ำบานเลื่อนแบบโค้ง K-17116T และ K-17116X/K-98641X



ชนิดกระจก

- C: กระจกเคลือบเคลือบโคท
- L: กระจกใส

สี/วัสดุเคลือบผิว:

- 0: สีขาว
- SHP: สีเงิน

สี/วัสดุเคลือบผิว อุปกรณ์:

- 0: สีขาว

นาทีโอ

ข้อมูลเฉพาะ

ผลิตภัณฑ์	น้ำหนัก
K-17116T/K-17116X	35 กิโลกรัม
K-98641X	50 กิโลกรัม




ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุขภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.

รุ่น	A	B
K-17116T-**	1850 มม.	872±7 มม.
K-17116X-**		
K-98641X-**	1900 มม.	972±7 มม.

ข้อสังเกต: ระยะการเปิดประตูมากที่สุด 460 มม.



ภาพแสดงผลิตภัณฑ์