

TWO-PIECE TOILET K-26064K


Features

- Vitreous china
- Round bowl
- Skirted bowl
- Back to wall
- Includes Wrapped seat
- Includes polished chrome push button
- Wash down flushing system
- Dual flush 2.6/4 liter per flush
- 185 mm rough-in for P-trap
- 610 x 406 x 780 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- SS 574



Technical Information

Fixture:	
Configuration	Two-piece, round-front
Water per flush	2.6/4 liter
Passageway	51 mm
Water area	124 x 101 mm
Water depth from rim	235 mm
Seat post hole centers	140 mm

Included Components:	
Bowl	K-26056K-**
Tank	K-26063K-**
Tank cover	1208785-SP-**
Wrapped seat	K-98724K-**
P-Trap Connector Assy	1138552-SP

Specified Model

Model	Description	Color/Finished
K-26064K	Reach Up 2PC BTW P-Trap , 2.6/4 L Wrapped seat	0: White


Installation Notes

Install this product according to the installation guide.

Recommended Accessories		
1548548-SP	Water Supply Hose, Stainless	N/A
1552115-SP	Shut Off Valve	CP: Polished Chrome
77837A-NA	S-Trap connector	N/A

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

Product Diagram