



McAllister®
23-1/2" undermount single-bowl kitchen sink, 20 pack
T11447

Features

- No faucet holes; requires wall- or counter-mount faucet
- 8" (203 mm) depth
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish
- Rectangular bowl
- 20 per pack
- Sink drain with strainer sold separately

Material

- Premium 20-gauge stainless steel

Installation

- Undermount
- Can be installed with or without reveal

Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer
K-23729 Stainless steel cleaner




Codes/Standards



ASME A112.19.3/CSA B45.4

STERLING® Stainless Steel Sinks **Lifetime Limited Warranty**

See website for detailed warranty information.



Mounting bracket assembly provides a secure installation.



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 27" (686 mm)

Bowl area (Only): Length: 23-3/8" (594 mm)
Width: 17-11/16" (449 mm)
Bowl depth: 8" (203 mm)
Water depth: 8" (203 mm)

Drain hole: 3-3/4" (95 mm)

Template: Undermount, 1315840-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.