



Springdale®

16-1/4" undermount single-bowl bar sink
T11448

Features

- No faucet holes; requires wall- or counter-mount faucet
- 8" (203 mm) depth
- 3-3/4" (95 mm) drain opening
- Stainless steel with luster finish

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer

11862 Sink Rack

K-23729 Stainless steel cleaner




Codes/Standards


ASME A112.19.3/CSA B45.4

STERLING® Stainless Steel Sinks Lifetime Limited Warranty


See website for detailed warranty information.





Mounting bracket assembly provides a secure installation.



Reveal



No Reveal



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 21" (533 mm)

Bowl area (Only): Length: 16-1/4" (413 mm)
Width: 17-3/4" (451 mm)
Bowl depth: 8" (203 mm)
Water depth: 8" (203 mm)

Drain hole: 3-3/4" (95 mm)

Template: Undermount, 1315843-7, required, included

Notes

Install this product according to the installation instructions.

Use the supplied cut-out template to select either a hidden or exposed rim.

Measure your actual product for roughing-in details.