

Cabinet Accessories
VT-SPOMM-L Lit Mag Mirror Specification Sheet

FEATURES

- Simple tool-less installation, adjustment, and position hold
- 5X magnification to help with detailed styling tasks
- Mirror tilt $\pm 25^\circ$ for personalized use
- Perimeter task light pattern
- Integrated dimming (hold) and selectable color (tap) control
- Energy efficient, collapsible LED mag mirror design
- Adjustable height via vertical cabinet track

Kelvin	2700K - 5600K
CRI	90+
R9 Value	50+

ELECTRICAL FEATURES


- Includes USB-C charging cord
- 3000mah internal li-ion battery for 4 hours of usage
- Auto shut-off feature conserves battery after 30 minutes

CONSTRUCTION


- Solid metal construction with a quality Matte Black finish

DIMENSIONS

- Width: 7-5/16" (186 mm)
- Height: 5-15/16" (150 mm)
- Depth: 2-1/2" (63.5 mm) Collapsed
- Depth: 13-1/4" (336 mm) Fully Extended



MORE INFORMATION



Scan the QR code to see the installation details found in the VT-SPOMM-L Lit Mag Mirror installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

INSTALLATION OPTIONS

- Compatible with with M Reserve (E2 & E4 only), Presence, and AiO Reserve Cabinets

