robern Vitality® Flip Wall Mirror - YM4836RIFPD3P - Specification Sheet

Features

- Front and side diffuser, no visible LED's
- Plug-in mirror, saves on install time
- All hardware with security bracket included
- Energy efficient LED lighting: (measurements may vary)

	Kelvin	3000**
-	CRI	90+
	Lumens* (Estimated)	1120
	R9 Value*	50+
	Watt Output - LED with optional defogger on	150w max

* Mirror measured not the raw LED.

** Starting in Fall 2021, Vitality Lighted Mirrors are being enhanced to 3000K CCT from 2700K CCT. Orders will be fullfilled with 3000K based on existing inventory.

Construction

- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware

Codes/Standards Applicable

Vitality Mirror is UL certified to:

- UL 962
- CSA-C22.2, No. 250.4

Dimensions

Height: 36" (914 mm) Width: 48" (1219 mm) Depth: 1-3/4" (45 mm)

Electrical System

• 120 Vac 60Hz wall outlet as shown in drawing

Options


• Mirror defogging


• Dimmable LED task lighting to 1%

• Compatible with most Triac/Phase-cut dimmers


Model Number Key

Vitality	Mirror	Width	Height	Shape	Light Pattern	Edge Type	Defogger	Color Temp	Options
Y	М	48	36	R = Rectangle	I = Inset	FP = Flat, Polished	D = Defogger	3 = 3000K	P = Flip
							Included		





⁺ See instructions for wiring and location



⁺ See instructions for wiring and location

YM4836RIFPD3P - Specification Sheet Page 2 of 2 CB-229-1420 | Jan. 14, 2022 Robern, Inc | 701 N. Wilson Ave. | Bristol, PA 19007