

8 7 6 5 4 3 2 1


REV	DATE	REVISION	BY	CHK
-	6-16-11	NEW DRAWING [80714-3]	CRS	

LEFT SIDE WALL



ENCLOSURE

J1 CONNECTIONS

1	1	(SCE-NO)
2	2	(BR-AC1)
3	3	(SCN-NO)
4	4	(TS-NC)
5	5	(BR-AC2)
6	6	(TS-EC)
7	7	(TS-EA)
8	8	(TB2-3)
9	9	(TB2-4)
10	10	(SE-C)
11	11	(TS-NB)
12	12	(TS-NA)
13	13	(SE-NO)
14	14	(SN-NO)
15	15	(TS-NC)
16	16	(TS-EC)
17	N/C	
18	18	(TS-EB)
19	19	(TS-LA)
20	20	(TS-LB)
21	21	(TS-LC)
22	22	(TS-NN)
23	23	(TS-EN)
24	24	(TS-LN)



- LEGEND**
- A3, A4 - AUXILIARY CONTACTS
 - BAT1 - BATTERY, 4.1V (THM-1550/HP)
 - BR - BRIDGE RECTIFIER
 - CNE - TRANSFER COIL (NORMAL/EMERGENCY)
 - J(#)-# - CONNECTOR (JACK)
 - K(#)-# - RELAY
 - P(#)-# - CONNECTOR (PLUG)
 - SCE - COIL CLEARING CONTACT (EMERGENCY)
 - SCN - COIL CLEARING CONTACT (NORMAL)
 - SE - SWITCH POSITION CONTACT (EMERGENCY POSITION)
 - SN - SWITCH POSITION CONTACT (NORMAL POSITION)
 - SW(#)-# - DIP SWITCH
 - TB(#)-# - TERMINAL BLOCK
 - TS - TRANSFER SWITCH
 - UIF - USER INTERFACE



MODEL RXT
100-200A 3P
STANDARD TRANSITION
FOR SCHEMATIC SEE GM80668

KOHLER CO.
POWER SYSTEMS, KOHLER, WI 53044 U.S.A.
THIS DRAWING IS UNLESS OTHERWISE SPECIFIED THE PROPERTY AND COPYRIGHT OF KOHLER CO. NO PART OF THIS DRAWING IS TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF KOHLER CO.

DIAGRAM, WIRING

APPROVALS	DATE	REV.	BY	CHK
CRS	6-16-11			
MTL	6-16-11	///		
MTL	6-16-11			

GM80667 1-1 D

8 7 6 5 4 3 2 1