


Features

- Acrylic and reinforced with fiberglass
- Drop-in
- 1700 x 750 x 530 mm

BATH
K-18345T



Codes/Standards Applicable

- Specified model meets or exceeds the following:
- ANSI Z124.1.2

Colors/Finishes

- 0: White

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-18345T	Evok oval plain bath	☐ 0
Required Accessories		
K-18355T	Bath drain	☐ CP

Product Specification:

The Evok bath shall be 1700 mm in length, 750 mm in width, and 530 mm in height. Bath shall be made of acrylic and reinforced with fiberglass. Bath shall be drop-in installation. Bath shall be Kohler Model K-18345T-_____.

EVOK OVAL

Technical Information

Fixture*:	
Basin area:	
Basin area bottom	1050 x 492 mm
Basin area top	1585 x 638 mm
To overflow:	
Water depth	411 mm
Capacity	238 liters
Drain hole	ø38 mm (1-1/2")
Overflow hole	ø52 mm
Weight	20 kg
*Approximate measurements for comparison only.	


Installation Notes

Install this product according to the installation guide.

Floor support under bath must provide for a minimum of 179 kg/square meter loading.

Dimensions are approximate.

Unit: mm.




Product Diagram

คุณลักษณะ

- อะครีลิกเสริมใยแก้ว
- แบบฝัง
- 1700 x 750 x 530 มม.

อ่างอาบน้ำ
K-18345T



มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI Z124.1.2

สี/วัสดุเคลือบผิว

- 0: สีขาว

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-18345T	อ่างอาบน้ำ รุ่น อีโวก ทรงรี	☐ 0

อุปกรณ์ที่จำเป็น		
K-18355T	สื่อดีอ่างอาบน้ำ	☐ CP

ข้อมูลผลิตภัณฑ์:

อ่างอาบน้ำอีโวกมีขนาดยาว 1700 มม. กว้าง 750 มม. และสูง 530 มม. ซึ่งผลิตจากวัสดุอะครีลิกเสริมใยแก้ว อ่างอาบน้ำติดตั้งแบบฝัง
อ่างอาบน้ำรุ่นนี้คือ อ่างอาบน้ำโคห์เลอส์รุ่น K-18345T-_____.

อีโวก ทรงรี



ข้อมูลเฉพาะ

สุขภัณฑ์:	
พื้นที่อ่างอาบน้ำ:	
พื้นที่ด้านล่าง	1050 x 492 มม.
พื้นที่ด้านบน	1585 x 638 มม.
ระดับน้ำล้น:	
ระดับน้ำลึก	411 มม.
ความจุน้ำ	238 ลิตร
รูท่อน้ำทิ้ง	Ø38 มม. (1-1/2")
รูท่อน้ำล้น	Ø52 มม.
น้ำหนัก	20 กิโลกรัม
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น	

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุขภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
พื้นที่ใช้รองรับอ่างอาบน้ำต้องสามารถรับน้ำหนักอย่างน้อย
179 กก./ตร.ม.

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์

อ่างอาบน้ำ รุ่น อีโวก....
หน้า 4/4
1119988-X4-A

KOHLER®