
KOHLER®

SANTA ROSA™

TOILET
K-3803

Features

- *Vitreous china*
- *Elongated bowl*
- *Ingenium® flushing system*
- *Polished chrome trip lever*
- *Includes seat and cover*
- *EPDM flapper*
- *Less supply*
- *12″ (305 mm) rough-in*
- *1.6 gpf (6 lpf)*
- *2″ (51 mm) glazed trapway*
- *9-3/4″ (248 mm) x 8-3/4″ (222 mm) water area*
- *27-1/2″ (699 mm) x 18-3/4″ (476 mm) x 27″ (686 mm)*



Codes/Standards Applicable

Specified model meets or exceeds the following:

- *ASME A112.19.2/CSA B45.1*
- *Energy Policy Act of 2005*

Colors/Finishes

- 0: White

Accessories

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Trip Lever	Colors/Finishes
K-3803	Toilet	left-hand	❑ 0

Recommended Accessories				
K-7637	Angle supply with stop	❑ CP	❑ PB	❑ Other_____

Optional Accessories			
K-9441	Trip lever (non-CP)	❑ PB	❑ Other_____

Product Specification

The elongated bowl toilet shall made of vitreous china. Toilet shall have 27-1/2″ (699 mm) in length, 18-3/4″ (476 mm) in width, and 27″ (686 mm) in height with a 9-3/4″ (248 mm) by 8-3/4″ (222 mm) water area. Toilet shall be 12″ (305 mm) rough-in and less supply. Toilet shall have an Ingenium® flushing system and an EPDM flapper. Toilet shall include a polished chrome trip lever, seat, and cover. Toilet shall have a 1.6 gpf (6 lpf) flow rate and 2″ (51 mm) glazed trapway. Toilet shall be Kohler Model K-3803-_____.

USA/Canada: 1-800-4KOHLER
(1-800-456-4537)
www.kohler.com

SANTA ROSA™


Technical Information

Fixture:	
Configuration	One-piece, elongated
Gallons per flush	1.6 gal (6 L)
Trapway	2″ (51 mm)
Water area	9-3/4″ (248 mm) x 8-3/4″ (222 mm)
Water depth from rim	6-1/4″ (159 mm)
Seat post hole centers	5-1/2″ (140 mm)

Included components:	
Tank cover	88497
Trip lever	87115
Toilet seat	K-4664
Tank accessory pack	52265
Bolt cap accessory pack	52048

Installation Notes

Install this product according to the installation guide.



Product Diagram

THE BOLD LOOK OF KOHLER®