# Stoneridge™ | K-CA33788-10L

60"-66" W x 80-1/4" H bypass shower door with 3/8"-thick Crystal Clear glass

## Features

- Frameless design emphasizes glass and creates a sleek, minimalist look
- Innovative roller design with stainless steel bearings simplifies installation and provides out-of-plumb adjustability while glass is installed
- External towel bar and internal vertical handle
- Cushioned center guide provides smooth, quiet sliding action
- Tempered glass ensures enhanced safety and durability
- Stay Closed bumpers press against glass to keep door firmly closed, providing excellent water containment
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Smooth, easy-to-clean wall jambs

## Available Colors/Finishes

***Color tiles intended for reference only.***

- SHP Bright Polished Silver
- BL Matte Black
- 2MB Vibrant Brushed Moderne Brass
- BNK Anodized Brushed Nickel



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 02:15 - US-CA

## Codes/Standards

ANSI Z97.1 (Tempered Glass)
CAN/CGSB-12.1
CPSC 16CFR 1201

## Technical Information

***All product dimensions are nominal.***

| | |
|---|---|
| Base-To-Wall Radius – Maximum: | 5/16" (8 mm) |
| Shower Ledge Minimum Flat: | 2-1/2" (64 mm) |
| Shower Wall Minimum Flat: | 3-7/16" (87 mm) |
| Weight: | 126 lbs (57.2 kg) |

## Material

- Frameless, 3/8" (10 mm) thick Crystal Clear tempered glass
- Anodized aluminum prevents rust and corrosion

## Warranty

***See website for detailed warranty information.***

KOHLER® Bath and Shower Doors Commercial One-Year Limited Warranty



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 02:15 - US-CA

THE BOLD LOOK OF KOHLER.




## Installation

- Fits opening widths 60" – 66" (1524 – 1676 mm)
- 80-5/16" (2040 mm) high, with a lofty 74-1/8" (1883 mm) minimum head clearance
- 6" (152 mm) width adjustment
- Out-of-plumb adjustability simplifies installation
- For residential and hospitality use

## Installation Notes

***Install this product according to the installation instructions.***

The vertical opening should be a minimum of 82-1/4" (2089 mm) to allow for installation clearance.



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 02:15 - US-CA

THE BOLD LOOK OF KOHLER