

Features


- Vitreous china
- Wall-mount
- Wall mounted fixing pack included
- Available in single-hole or 8" centers
- With overflow
- 550 x 450 x 220 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- AS/NZS 1730:1996
- AS1589-2001
- TIS 791-2544

WALL-HUNG LAVATORY K-77767K



Technical Information

Fixture:	
Basin area	520 x 313 mm
Water depth	165 mm
Usable Water Volume	12 Liter
Drain hole	44 mm D.
*Approximate measurements for comparison only.	

Included Components:	
Wall mounted fixing pack	1049141

Installation Notes

Install this product according to the installation guide.

Specified Model


Model	Description	Color/Finishes
K-77767K-1	Modern Life wall-hung lavatory, single-hole	0: White
K-77767K-8	Modern Life wall-hung lavatory, 8" centers	0: White
K-77767K-ZS	Modern Life 12L lavatory, 1 hole	0: White

Recommended Accessories		
K-7119T	Click drain	CP: Polished chrome
K-9071T	Bottle-trap	CP: Polished chrome


Dimensions are approximate. (Do not direct measure a dimensional from picture below)

Unit: mm

K-77767K-1 / K-77767K-ZS



K-77767K-8



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- สุกษณิกพิเศษวามิกประภาหวิเทรียสไชน่า (Vitreous china)
- ติดตั้งแบบแขวนผนัง
- พร้อมชุดนอตยึดอ่างล่างหน้า
- แบบเจาะรูเดี่ยว หรือแบบเซ็นเตอร์ 8"
- พร้อมมูน้ำล้น
- 550 x 450 x 220 มม.

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ASME A112.19.2/CSA B45.1
- AS/NZS 1730:1996
- AS 1589-2001
- มอก. 791-2544

ข้อมูลเฉพาะ


ลักษณะ	
พื้นที่ใช้งานในอ่างล้างหน้า	520 x 313 มม.
ระยะน้ำลึก	165 มม.
ความจุน้ำในอ่างล้างหน้า	12 ลิตร
ขนาดรูเสียบท่ออ่าง	เส้นผ่าศูนย์กลาง 44 มม.
*ขนาดระยะโดยค่าประมาณเพื่อการเปรียบเทียบเท่านั้น	

ส่วนประกอบผลิตภัณฑ์

ชุดนอติยัดอ่างล้างหน้า	1049141
------------------------	---------

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสภากันท์โดยใช้คีมอเนาะนำการติดตั้ง



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-77767K-1	อ่างล้างหน้าแขวนผนัง แบบเจาะรูเดียว รุ่น โมเดิร์น โลหิ	0: สีขาว
K-77767K-8	อ่างล้างหน้าแขวนผนัง แบบเซ็นเตอร์ 8" รุ่น โมเดิร์น โลหิ	0: สีขาว
K-77767K-ZS	อ่างล้างหน้าแขวนผนัง รุ่น โมเดิร์น โลหิ	0: สีขาว


อุปกรณ์แนะนำ

K-7119T	สะดืออ่างล้างหน้าแบบกด	CP: สีโครมเงา
K-9071T	พ่อน้ำทิ้งอ่างล้างหน้าแบบกระปุก	CP: สีโครมเงา


ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.

K-77767K-1 / K-77767K-ZS



K-77767K-8



หมายเหตุ: ระยะเวลาแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์