

### ONE-PIECE TOILET WITH SEAT K-77739X


#### Features

- Vitreous china
- Round-front bowl
- Includes quiet close seat
- Includes polished chrome trip lever
- Class Five+ dual flush system
- 3/4.5 liter per flush
- 305 mm rough-in for S-trap
- 700 x 365 x 737 mm

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 792-2554



#### Technical Information

Fixture:	
Configuration	one-piece, round-front
Water per flush	3/4.5 liter
Passageway	49 mm
Water area	235 x 193 mm
Water depth from rim	143 mm
Seat post hole centers	140 mm

Included Components:	
Tank cover	1265630-SP-*
Quiet close seat	77380X-*


#### Installation Notes

Install this product according to the installation guide.

#### Specified Model

Model	Description	Color/Finished
K-77739X-SL	Modern Life 1-PC 3/4.5L Dual Flush Toilet with Quiet Close Seat	0: White

Dimensions are approximate.  
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

#### Product Diagram

### สุขภัณฑ์ชิ้นเดียวพร้อมฝารองนั่ง K-77739X


#### คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทวิเทียสไชน่า (Vitreous china)
- โถสุขภัณฑ์แบบหน้าสั้น
- พร้อมก้านกดชำระโลหะชุบโครเมียม
- ระบบชำระล้างแบบคลาสไฟว์พลัส คูอัลพลัส
- ใช้น้ำในการชำระล้าง 3/4.5 ลิตร
- ระยะจุดกึ่งกลางท่อน้ำทิ้งถึงผนัง 305 มม. สำหรับการติดตั้งท่อน้ำทิ้งลงพื้น
- 700 x 365 x 737 มม.

#### มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 792-2554



#### ข้อมูลเฉพาะ

สุขภัณฑ์	
ลักษณะ	สุขภัณฑ์ชิ้นเดียว, หน้าสั้น
การใช้น้ำชำระล้างต่อครั้ง	3/4.5 ลิตร
ขนาดท่อน้ำทิ้ง	49 มม.
ผิวหน้าน้ำ	235 x 193 มม.
ความลึกจากขอบโถสุขภัณฑ์ถึงผิวหน้าน้ำ	143 มม.
ระยะห่างระหว่างรูยึดฝารองนั่ง	140 มม.

ส่วนประกอบสุขภัณฑ์	
ฝาปิดถังพักน้ำ	1265630-SP-*
ฝารองนั่งแบบกันกระแทก	77380X-*

#### ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งสุขภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

#### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-77739X-SL	สุขภัณฑ์แบบชิ้นเดียว ใช้น้ำ 3/4.5 ลิตร รุ่น โมเดิร์นไลฟ์พร้อมฝารองนั่งแบบกันกระแทก	0: สีขาว

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

#### ภาพแสดงผลิตภัณฑ์