

### Features


- Vitreous china
- Elongated bowl
- Includes French Curve quiet close seat
- Includes polished chrome trip lever
- Siphonic Wash Down flushing system
- 4 liter per flush
- 305 mm rough-in for S-trap
- 423 x 725 x 746 mm

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- MS1552:2011
- PNS156:2010
- SNI03-0797:2006
- SS574:2012
- TIS 792-2554

## TWO-PIECE TOILET WITH SEAT K-22248K



### Technical Information

|                        |                      |
|------------------------|----------------------|
| Fixture:               |                      |
| Configuration          | two-piece, elongated |
| Water per flush        | 4 liter              |
| Passageway             | 51 mm                |
| Water area             | 137 x 109 mm         |
| Water depth from rim   | 235 mm               |
| Seat post hole centers | 140 mm               |

|                               |            |
|-------------------------------|------------|
| Included Components:          |            |
| Bowl                          | K-22246K   |
| Tank                          | K-9992X    |
| Tank cover                    | 1277508-SP |
| French Curve quiet close seat | K-4713X    |

### Installation Notes


Install this product according to the installation guide.

### Specified Model

| Model      | Description                                                         | Color/Finished |
|------------|---------------------------------------------------------------------|----------------|
| K-22248K-C | Adair Concealed two-piece toilet with French Curve quiet close seat | 0: White       |

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at anytime without notice.

### Product Diagram

## คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทวิเทรียสไชน่า (Vitreous china)
- โถสุขภัณฑ์แบบหน้ายาว
- พร้อมฝารองนั่งเฟรนช์เคิร์ฟแบบกันกระแทก
- พร้อมก้านกดชำระโลหะชุบโครเมียม
- ระบบชำระล้างแบบไฮฟอนนิค วอชดาวน์
- ใช้น้ำในการชำระล้าง 4 ลิตร
- ระยะจุดกึ่งกลางท่อน้ำทิ้งถึงผนัง 305 มม. สำหรับการติดตั้งท่อน้ำทิ้งลงพื้น
- 423 x 725 x 746 มม.

## มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ASME A112.19.2/CSA B45.1
- MS1552:2011
- PNS156:2010
- SNI03-0797:2006
- SS574:2012
- มอก. 792-2554

## ข้อมูลเฉพาะ

| สุขภัณฑ์                          |                          |
|-----------------------------------|--------------------------|
| ลักษณะ                            | สุขภัณฑ์สองชั้น, หน้ายาว |
| การใช้น้ำชำระล้างต่อครั้ง         | 4 ลิตร                   |
| ขนาดท่อน้ำทิ้ง                    | 51 มม.                   |
| ผิวหน้า                           | 137 x 109 มม.            |
| ความลึกจากขอบโถสุขภัณฑ์ถึงผิวหน้า | 235 มม.                  |
| ระยะห่างระหว่างรูยึดฝารองนั่ง     | 140 มม.                  |

| ส่วนประกอบสุขภัณฑ์                |            |
|-----------------------------------|------------|
| โถสุขภัณฑ์                        | K-22246K   |
| ถังพักน้ำ                         | K-9992X    |
| ฝาปิดถังพักน้ำ                    | 1277508-SP |
| ฝารองนั่งเฟรนช์เคิร์ฟแบบกันกระแทก | K-4713X    |

## ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งสุขภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

## รุ่นผลิตภัณฑ์

| รุ่น       | ชื่อผลิตภัณฑ์                                                                         | สี/วัสดุเคลือบผิว |
|------------|---------------------------------------------------------------------------------------|-------------------|
| K-22248K-C | สุขภัณฑ์สองชั้น แบบทอลงพื้น รุ่น อะแดร์ คอนซีล พร้อมฝารองนั่งเฟรนช์เคิร์ฟแบบกันกระแทก | 0: สีขาว          |

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง  
บริษัทฯ ขอสงวนสิทธิ์ในการเปลี่ยนแปลงข้อมูลผลิตภัณฑ์ บรรจุภัณฑ์ที่มีโดยมิต้องแจ้งให้ทราบล่วงหน้า

## ภาพแสดงผลิตภัณฑ์