

Features

- Brass construction.
- Leak-free ceramic disc valve(s) with lifetime warranty.
- Durable KOHLER finishes resist corrosion and tarnishing.
- 110 mm spout reach (K-EX27027T-4).
- Adjustable inlet fittings with 15 mm tolerance.
- Includes 3-function handshower.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- TIS 2066-2552

Installation Notes

Install this product according to the installation guide.


EXPOSED WALL-MOUNT SHOWER MIXER K-EX27026T-4, K-EX27027T-4



Specified Model


Model	Description	Colors/Finishes	
K-EX27026T-4	Occasion exposed wall-mount shower mixer	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others
K-EX27027T-4	Occasion exposed wall-mount bath shower mixer	<input type="checkbox"/> CP: Polished Chrome	<input type="checkbox"/> Others

For a full range of color finishes in your market, please contact your local Kohler representative.



Flow Curve (Bath outlet)

K-EX27027T-4




Flow Curve (Handshower)


K-EX27026T-4, K-EX27027T-4

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimension from picture below.)
Unit: mm



K-EX27026T-4



K-EX27027T-4

Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคโธเลอรัคทนเงางาม
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 110 มม. (K-EX27027T-4)
- อุปกรณ์ติดตั้งกับท่อน้ำเข้า ปรับระยะได้ 15 มม.
- พร้อมฝักบัวสายอ่อนปรับสายน้ำ 3 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552 • GB 18145-2014

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


ก๊อกผสมลงอ่างอาบน้ำและยืนอาบ แบบติดผนังพร้อมฝักบัวสายอ่อน K-EX27026T-4, K-EX27027T-4




รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-EX27026T-4	ก๊อกผสมยืนอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นโอเคชั่น	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> อื่นๆ
K-EX27027T-4	ก๊อกผสมลงอ่างอาบน้ำและยืนอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นโอเคชั่น	<input type="checkbox"/> CP: สีโครมเงา	<input type="checkbox"/> อื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคโธเลอรัคในประเทศของท่าน



K-EX27027T-4



K-EX27026T-4, K-EX27027T-4

หมายเหตุ: อัตราการไหลโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

