Mira React BSM

Thermostatic Bath Shower Mixer (Deck Mounted)

SUITABLE FOR ALL SYSTEMS

5 YEAR WARRANTY

The perfect blend of easy accessibility, precision technology and understated style.



Product Information

Description	Colour	Product No.
Mira React Deck Mount BSM	Chrome	1.1900.019
Mira React Deck Mount BSM Valve Only	Chrome	1.1900.020

Features & Benefits

Temperature control
Thermostatic temperature stability
Easy to fit
Standard deck mount, easy fit elbows
Slide bar with adjustable fixing centres (400 - 520 mm)
For your customer
Compatible with all systems, even at low pressure
Separate flow and temperature controls
Deck mount elbows allow bath-edge installation
Temperature control has maximum temperature stop for increased safety (with override for a hotter shower)
Flow control incorporates diverter to allow easy switch between shower and bathfill
Mira Cool Shield™ to ensure valve doesn't get hot to touch during use
One spray 9cm showerhead with rub-clean nozzles
1.75m flexible shower hose

mira SHOWERS

Product Specification


Tech Details

Temperature and flow control
Temperature control type: Thermostatic
Flow control type: Ceramic
Installation
Deck mounted easy fit elbows, supports 2nd fix valve installation.
Inlet connections: 3/4" BSP male under bath connections to pipework; 3/4" BSP connection to mixer shower
Outlet connections to shower: 1/2" BSP Male
Reversed inlets supported: No - hot left, cold right only
Supply Conditions (hot and cold)
Cold water range: 1°C to 25°C
Hot water range: Min 55°C; 60°C - 65°C (recommended)
Minimum maintained pressure (gas water heater) : 1 bar (10 metre head)
Minimum maintained pressure (gravity system) : 0.1 bar (1 metre head)
Maximum maintained pressure: 5.0 bar (50 metre head)
Maximum static pressure: 10.0 bar (100 metre head)

Performance
Flow rate (at handset): 9 l/min at 0.5 bar Flow rate (at bath outlet): 15 l/min at 0.6 bar
Flow regulator: 6 l/min (for handset only, supplied with product)
Temperature stability: ± 2°C
Safety Features
Automatic shutdown: Shutdown within 2 secs
Factory set to safe max temp: 39°C at maximum temperature stop (ideal for showering), 46°C using override (ideal for bathfil)*
Adjustable maximum temperature for on-site conditions
Approvals
KIWA UK approved product
WRAS approved (Water Regulations Advisory Scheme)
TMV2 approved product

*Preset to a safe temperature under ideal conditions at the factory, appropriate for most systems. Site conditions and personal preference may make it necessary to reset this temperature.

Dimensions



www.mirashowers.co.uk/expert