


14661T-4 8"脸盆龙头



\*\*订购时请说明颜色编号

**\*\*Color code must be specified when ordering**

# 安装说明书

14661T-4 8"脸盆龙头

## **BEFORE YOU BEGIN**

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

### 注意事项:

- 1.一定要先彻底冲洗供水管以清除管道中的杂质。
  - 2.检查供水管有无损坏。如需要，进行替换。
  - 3.尽可能在安装脸盆之前安装水龙头。

**4.龙头最高工作压力：0.4MPa(4bar)。水压超过0.4MPa(4bar)须安装减压阀，否则可能损坏龙头。**

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer.  
They contain important information.

## **NOTES:**


1. Flush the water supply pipes thoroughly to remove debris.
  2. Inspect the supply tubing for damage. Replace as necessary.
  3. If possible, install this faucet before installing the lavatory.
  - 4. The highest working pressure for faucet is 0.4MPa(4bar). If it exceeds 0.4MPa(4bar), a pressure reducer is needed. Or maybe damage the faucet.**

使用说明

逆时针旋转左把手为开，顺时针旋转右把手为开。

Left handle opens with turning counter-clockwise.  
Right handle opens with turning clockwise.


#### **ROUGH IN DIMENSIONS**



## 安装说明

### 如何安装出水口


从出水口组件(1)上取下T型接头(8)、螺母(4)和钢垫(3)。注意：限流器(5)不允许取出，并要定期清理。将橡胶垫片(6)和塑料垫片(7)留在T型接头内。



将橡胶垫片(2，外径45mm)装到出水口装饰盖底部凹槽，然后将出水口装于脸盆中孔。从脸盆下方安装钢垫(3)和螺母(4)。找正出水口，用扳手拧紧螺母固定出水口组件。装回T型接头。

### 如何安装阀体和把手

先从阀体组件(16)上取下装饰盖底座(12)、橡胶垫片(13)、钢垫(14)和固定环(15)。将钢垫(14)和固定环(15)装到阀体上。保持螺杆(17)扳手孔朝下，旋到固定环上。将橡胶垫片(13)装到装饰盖底座底部凹槽，将装饰盖底座装入脸盆安装孔。从脸盆下方将阀体组件装入装饰盖底座(注：带红色标记的阀体组件装在左侧)。根据软管安装需要适当调整阀体出水口朝向。用3mm的六角扳手(19)锁紧螺杆以固定阀体。锁紧螺母(18)。




将把手组件(9)安装到装饰盖底座(注意：带有红色标记的把手组件装在左侧，且安装前阀芯处于关闭状态)。用2mm六角扳手(11)将螺钉(10)锁紧固定把手。

阀处于关闭位置把手的状态如图示。

### 如何连接软管

将软管(21)两端放上垫片(20)，连接阀体组件(16)的出水口和T型接头(8)。

注意：软管(21)只能用于此处。



## INSTALLATION

### How To Install The Spout

Remove the center tee(8), nut(4) and steel washer(3) from the spout kit(1). **Note:** Don't take out the flow restrictor(5) in the spout kit and clear it regularly. Leave the rubber washer(6) and plastic gasket(7) in the center tee.

Put the rubber washer(2, external diameter 45mm) into the bottom groove of the spout kit escutcheon. Then fit the spout kit into the center hole of lavatory. From underside of the lavatory, install the steel washer(3) and nut(4). Position the spout. Secure the spout kit by tightening nut. Reinstall the center tee.

### How To Install The Side Bodies And The Handles

Remove the escutcheon bases(12), the rubber washers(13), the steel washers(14) and the threaded rings(15) from side bodies(16). Install the steel washers(14) and the threaded rings(15) onto the side bodies. Keep the wrench holes of the studs(17) facing downwards, thread them onto the threaded ring. Put the rubber washers(13) into the bottom groove of the escutcheon bases. Fit the escutcheon bases into the mounting holes of the lavatory. From the underside of the lavatory, install the side bodies onto the escutcheon bases(**Note:** the side bodies with red mark should be installed on the left side). Adjust the outlets of side bodies to connect hoses easily. Secure the side bodies by tightening studs with 3mm hex wrench(19). Tighten the nuts(18) onto the studs.

Place the handle kits(9) onto the escutcheon bases with the valves closed(**Note:** The handle kit with red mark should be installed on the left side). Secure handle kits by tightening the screws(10) with 2mm hex wrench(11).

The illustration shown is the correct position of the handles in the off position.

### How To Connect Hoses

Connect the outlets of the side bodies(16) and the center tee(8) with the hoses(21) and washers(20).


**NOTE:** The hoses(21) should only be used here.

### 如何安装排水器

将锁紧螺母(26)、塑料垫片(25)、橡胶垫圈(24)从排水本体上依次取下。把排水本体从脸盆上部孔插入。再依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从排水本体底部装入。锁紧螺母。

**注意：**如果需要，可直接在排水器法兰(22)底面沿周围涂一圈密封油灰或其他密封剂，而不使用橡胶垫片(23)。

在锁紧螺母拧紧后，不可调整排水本体的位置，否则会破坏油灰密封或密封剂密封。去除多余的油灰。



## How To Install The Drain

Remove the locknut(26), plastic washer(25), rubber gasket(24) from the drain body. Insert the drain body into the lavatory. Reinstall the rubber gasket(Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut.

**NOTE:** If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(22), instead of using rubber washer(23).



Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal. Remove any excess putty.

### 安装结果检查

检查并确保所有的衔接处都已拧紧。确保手柄处于关闭位置。

打开排水系统和主要供水源，检查并修理有漏水的接口。

用1.5mm六角扳手(27)旋松螺钉(30)，用工具(28)小心地卸下起泡器(29)，打开水龙头，让水流过出水口一分钟以清除杂质。冲洗起泡器，关闭水龙头，保持固定孔朝下重新装回起泡器。



Ensure that all connections are tightened and the handle is in the off position.

Open the drain. Turn on main water supply and check for leaks. Repair as required.

Loosen screw(30) with 1.5mm hex wrench(27). Remove the aerator(29) carefully with key(28). Turn on the faucet. Run the water through the spout for about one minute to remove any debris. Remove any debris from the aerator. Shut off the faucet. Keep the fixing hole facing downwards, reinstall the aerator.

### Replacing The Washer & Piston Kit

Turn counterclockwise to remove the stopper(31). Take out washer(32). Replace with a new one. Turn counterclockwise to remove the piston kit(33). Replace with a new one. Reinstate stopper and washer.

### 清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

### CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.