


22569T-B4 双把墙出水脸盆龙头_不含阀芯(出水嘴长168mm)

22570T-B4 双把墙出水脸盆龙头_不含阀芯(出水嘴长218mm)



**订购时请说明颜色编号

**Color code must be specified when ordering

22569T-B4 双把墙出水脸盆龙头_不含阀芯(出水嘴长168mm)

22570T-B4 双把墙出水脸盆龙头_不含阀芯(出水嘴长218mm)

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。



注意事项：

1. 一定要先彻底冲洗供水管以清除管道中的杂质。
2. 检查供水管有无损坏和漏水。如需要，进行替换和维修。
3. 遵守当地管路安装条例。
4. 本产品需与双把墙出水脸盆龙头阀芯31141T-NA搭配使用。
5. 确保安装此产品之前，双把墙出水脸盆龙头阀芯31141T-NA已安装完毕。

使用说明

逆时针旋转左把手为热水，顺时针旋转右把手为冷水。

安装尺寸



BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.



NOTES:

1. Flush the water supply pipes thoroughly to remove debris.
2. Inspect the supply tubing for damage and leakage. Replace and maintain as necessary.
3. Observe local plumbing codes.
4. These products should match with the wall mount lavatory faucet valve 31141T-NA.
5. Install the wall mount lavatory faucet valve 31141T-NA before installing these products.

HANDLE OPERATION


Turn the left handle counter-clockwise for hot water, turn the right handle clockwise for cold water.

ROUGH-IN DIMENSIONS



安装步骤

INSTALLATION




如何安装把手

墙壁装修好后，去掉31141T-NA上的阀体保护套。

如图1所示，将橡胶垫片(1)装到装饰盖底座(2)背部凹槽中，用工具(3)将装饰盖底座旋到阀体上并贴紧墙壁。将齿套(4)安装到阀芯(5)上，用螺钉(6)锁紧。

如图2所示，将把手组件(7)安装到装饰盖底座(2)上。**注意：**有红色标记的把手组件装左侧且安装之前阀芯处于关闭状态。用2mm六角扳手(8)锁紧把手组件内的螺钉(9)以固定把手组件。




How to Install the Handles

Remove the valves protectors from 31141T-NA after the wall is finished.

As shown in figure 1, put the rubber washers(1) into the rear groove of the escutcheon bases(2). Screw the escutcheon bases onto the valves with key(3) until it is against the finished wall. Install the stems(4) onto the valves(5), and then tighten them with screws(6).

As shown in figure 2, place the handle kits(7) onto the escutcheon bases(2) with the valves closed. **NOTE:** The handle kit with red mark should be installed on the left side. Tighten the screws(9) with 2mm hex wrench(8) to secure the handle kits.




如何安装出水口

去掉31141T-NA上的出水口保护套。

如图3所示，用8mm六角扳手(10)将接头(11)旋紧到阀体上。用3mm六角扳手(12)旋松出水口(13)的底部螺钉(14)。确保垫片(15)已嵌入装饰罩(16)背面凹槽中，将出水口出口朝下安装到接头(11)上，使其紧贴墙面。用六角扳手锁紧螺钉到出水口底部，固定出水口。**注意：**不要划伤接头上的O型圈(17)。

阀芯处于关闭位置时，出水口和把手安装完毕状态如图4所示。



How to Install the Spout

Remove the spout protector from 31141T-NA after the wall is finished.

As shown in figure 3, screw the connector(11) into the valve body with 8mm hex wrench(10). Loosen the screw (14) in the spout(13) bottom with 3mm hex wrench(12). Ensure the washer(15) is put into the groove of the escutcheon(16) backside. Install the spout onto the connector(11) with its outlet downwards until it is against the finished wall. Tighten the screw with hex wrench to secure the spout. **NOTE:** Don't damage the O-ring(17) on the connector.

When the installation is completed, the correct position of the spout and handles with the valve closed is shown in figure 4.

如何安装排水器


How to Install the Drain

把锁紧螺母(18)、塑料垫片(19)、橡胶垫圈(20)和尾管(21)从排水本体上依次取下。在尾管螺纹处须缠绕足以密封的密封胶或涂合适的密封胶，装回排水本体。

把排水本体从脸盆上部孔插入。再依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从排水本体底部装入。将锁紧螺母锁紧。

注意：在锁紧螺母拧紧后，不可调整排水本体的位置，否则会破坏油灰密封或密封胶密封。

注意：如果需要，可直接在排水器盘片(22)底面沿周围涂一圈密封油灰或其他密封剂，而不使用橡胶垫片(23)。



Remove the locknut(18), plastic washer (19), rubber gasket(20) and tailpiece (21) from the drain body. Supply enough tape or sealant to tailpiece thread. Reinstall the tailpiece.

Insert the drain body into the lavatory. Put the rubber gasket(Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut.

NOTE: Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal.


NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(22), instead of using rubber washer(23).

安装结果检查

INSTALLATION CHECKOUT

检查并确保所有衔接螺母都已拧紧，确保把手在关闭位置。打开排水器和主要供水源，检查是否有漏水。如有漏水，修理之。

用工具(24)拆下起泡器(25)。打开水龙头冷热水，让水流出约一分钟以清除杂质，检查渗漏。冲洗起泡器，关闭水龙头，重新装回起泡器。



Ensure that all connections are tighten. Ensure the handles are in the off position. Turn on the drain and main water supply, and check for leaks. Repair as needed.

Remove the aerator(25) with tool(24). Turn on the faucet. Run hot and cold water through the spout for about one minute to remove any debris. Check for leaks. Remove any debris from the aerator. Shut off the faucet. Reinstall the aerator.

清洗说明

CLEANING INSTRUCTIONS

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可适用于科勒牌的水龙头及其配件上。

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.