


柏诗

COMPOSED

零 件 图

2 Handles Wall Mount Lavatory Faucet without Valve

73067T-B3 双把墙出水脸盆龙头_不含阀芯(十字把手) 73067T-B4 双把墙出水脸盆龙头 不含阀芯(杆型把手)



^{**}订购时请说明颜色编号

KOHLER®

COMPOSED

安装说明书

2 Handles Wall Mount Lavatory Faucet without Valve

73067T-B3 双把墙出水脸盆龙头_不含阀芯(十字把手) 73067T-B4 双把墙出水脸盆龙头_不含阀芯(杆型把手)

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

INSTALLATION INSTRUCTIONS

说明书包括重要的安装、保养及清洁方面的内容,请把 这些资料交给用户阅读。

注意事项:

- 1. 一定要先彻底冲洗供水管以清除管道中的杂质。
- 2. 检查供水管有无损坏和漏水。如需要,替换和维修之。
- 3. 遵守当地管路安装条例。
- 4.73067T-B4需与双把墙出水脸盆龙头阀芯31141T-NA搭配使用;73067T-B3需与双把墙出水脸盆龙头阀芯34667T-NA搭配使用。
- 5. 确保安装此产品之前,双把墙出水脸盆龙头阀芯31141T-NA或34667T-NA已安装完毕。

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

NOTES:

- 1. Flush the water supply pipes thoroughly to remove debris.
- 2. Inspect the supply tubing for damage and leakage. Replace and maintain as necessary.
- 3. Observe local plumbing codes.
- 4. 73067T-B4 should match with the wall mount lavatory faucet valve 31141T-NA. 73067T-B3 should match with the wall mount lavatory faucet valve 34667T-NA.
- 5. Install the wall mount lavatory faucet valve 31141T-NA or 34667T-NA before installing these products.

使用说明

对于**73067T-B3**,顺时针旋转左把手为热水,逆时针旋转右把手为冷水。

对于73067T-B4, 逆时针旋转左把手为热水, 顺时针旋转右把手为冷水。


HANDLE OPERATION

For 73067T-B3, turn the left handle clockwise for hot water, turn the right handle counter-clockwise for cold water.

For 73067T-B4, turn the left handle counter-clockwise for hot water, turn the right handle clockwise for cold water.


安装尺寸

ROUGH-IN DIMENSIONS




1482027-T2-A **4** 1482027-T2-A **1**

^{**}Color code must be specified when ordering



安装步骤

INSTALLATION



6 O TO

如何安装把手

墙壁装修好后,去掉31141T-NA或34667T-NA上的阀体保护套。

如图1所示,将齿套(2)安装到阀芯(1)上,用螺钉(3)锁紧。确保阀芯处于关闭状态。将把手(4)安装到齿套上,并旋转把手底座直至与墙面接触。

注意: 有红色标记的把手装左侧。

如何安装出水口

去掉31141T-NA或34667T-NA上的出水口保护套。

如图2所示,用8mm六角扳手(5)将接头(6)旋紧到阀体上。将装饰盖(7)装到接头上并贴紧墙面。注意:不要划伤接头上的O型圈(8)。

用2mm六角扳手(9)旋松出水口(10)的底部螺钉(11)。将出水口出口朝下安装到接头上,使其紧贴装饰盖,锁紧螺钉,固定出水口。

How to Install the Handles

Remove the valves protectors from 31141T-NA or 34667T-NA after the wall is finished.

As shown in figure 1, install the stems(2) onto the valves(1), and then tighten them with screws(3). Ensure the valves are closed. Slide the handles(4) onto the stems and screw handle bases until they are against the finished wall.


NOTE: The handle with red mark should be installed on the left side.

How to Install the Spout

Remove the spout protector from 31141T-NA or 34667T-NA after the wall is finished.

As shown in figure 2, screw the connector(6) into the valve body with 8mm hex wrench(5). Install the escutcheon(7) onto the connector until it is against the finished wall. **NOTE:** Don't damage the O-ring(8) on the connector.


Loosen the screw(11) in the spout(10) bottom with 2mm hex wrench(9). Install the spout onto the connector with its outlet downwards until it is against the connector. Tighten the screw to secure the spout.



73067T-B3

阀芯处于关闭位置时, 出水口和把手安装完毕状态如图所示。





73067T-B4

When the installation is completed, the correct position of the spout and handles with the valve closed is shown in figure.


如何安装排水器

把锁紧螺母(12)、塑料垫片(13)、橡胶垫圈(14)和尾管(15)从排水本体(16)依次取下。在尾管螺纹处须缠绕足以密封的密封胶带或涂合适的密封胶,并装回排水本体。

把排水本体从脸盆上部孔插入。再依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从脸盆下方装回到排水本体上。锁紧螺母。

注意: 如果需要,可直接在法兰盘(17) 底面沿周围涂一圈密封油灰或其它密封剂,而不使用橡胶垫片(18)。

在锁紧螺母拧紧后,不可调整排水本体位置,否则会破坏油灰或密封剂密封。



How to Install the Drain

Remove the locknut(12), plastic washer (13), rubber gasket(14) and tailpiece(15) from the drain body(16). Supply enough tape or sealant to tailpiece thread. Reinstall the tailpiece.

Insert the drain body into the lavatory.
Install the rubber gasket(Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut.

NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(17), instead of using rubber washer(18).


Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal.

安装结果检查

检查并确保所有衔接螺母都已拧紧, 确保把手在关闭位置。

打开排水器和主要供水源,检查是否 有漏水。如有漏水,修理之。

用工具(19)拆下起泡器(20)。打开水龙 头冷热水,让水流出约一分钟以清除 杂质,检查渗漏。冲洗起泡器,关闭 水龙头,重新装回起泡器。



INSTALLATION CHECKOUT

Ensure that all connections are tight.
Ensure the handles are in the off position.

Turn on the drain and main water supply, and check for leaks. Repair as needed.

Remove the aerator(20) with tool(19). Turn on the faucet. Run hot and cold water through the spout for about one minute to remove any debris. Check for leaks. Remove any debris from the aerator. Shut off the faucet. Reinstall the aerator.

清洗说明

适用于所有加工处理过的表面:以中性肥皂水清洗镀层表面,再以干净的软布彻底擦干整个表面,许多清洁剂,比如氨水、去污粉及洁厕灵等,会对电镀表面造成伤害,切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水 龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

1482027-T2-A **2** 1482027-T2-A **3**