


安装步骤

如何安装水龙头

若因维修或其它原因拆下软管(4)，装回时手动拧紧即可。将固定螺杆(3)安装到水龙头(1)底部孔中，将垫片(2)穿过软管、固定螺杆和提拉线缆(5，仅对于**37327K**)末端嵌入到水龙头底部槽中。

将水龙头组件插入脸盆安装孔中，使水龙头底部接触台面。调整水龙头，从脸盆下方依次将垫片(6，橡胶垫片放在上面)穿入固定螺杆，锁紧螺母(7)以固定水龙头。

把软管接到水源，当面对水龙头时，左边接热水源，右边接冷水源，冷水管贴有“COLD”签。



INSTALLATION

How to Install the Faucet

If need to take off the hoses(4) to repair, reinstall and tighten them by hand. Install the mounting stud(3) to the thread hole of the faucet(1) bottom. Slide the washer (2) over the hoses, mounting stud and cable end(5, only for **37327K**) until it is put into the groove of the faucet bottom.

Insert the faucet assembly into the lavatory hole until the faucet bottom is against the deck. Position the faucet. From underside of the lavatory, place the washers(6, rubber washer is on the top) onto the mounting stud. Secure the faucet by tightening nut(7).

Attach the hoses to water supplies. When facing front of the faucet, the left hose should be connected to hot water, the right hose with "COLD" label should be connected to cold water.

如何安装排水器
(仅对于**37327K**)

将止水塞(8)、法兰盘(9)及垫片(10)从排水本体(12)取下。把排水本体组件从脸盆下方插入排水孔中，调整至合适的位置，再将法兰盘(9)带垫片(10)旋到排水本体上。



用扳手拧紧排水本体上的锁紧螺母(11)。把止水塞(8)放入排水组件。

注意：如果需要，可直接在法兰盘(9)底面沿周围涂一圈密封油灰或其它密封剂，而不使用垫片(10)。

打开排水本体上的盖板(13)，将提拉线缆末端(14)嵌入拉线盒(15)内部的方孔(16)中。使其在拉线盒两端(A, B)卡到位，如图所示。

然后用手扣紧盖板(13)。装好后请拉动提拉头(17)，确保其正常工作。

注意：在锁紧螺母拧紧后，如法兰盘使用密封油灰或其它密封剂，则不可以调整排水本体的位置，否则会破坏油灰密封的密封性。同时去除多余油灰。



How to Install the Drain
(Only for **37327K**)

Remove the stopper(8), flange(9) and washer(10) from the drain body(12). Insert the drain body through the drain hole from underside, and adjust the position properly. Screw the flange(9) with washer(10) onto the drain body.

Tighten the locknut(11) on the drain body with wrench. Insert the stopper(8) into the drain assembly.

NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(9), instead of using washer(10).

Open the coverplate(13) on the drain body, and insert cable end(14) into the square hole(16) of the cable box(15). Make sure the cable is properly buckled at both ends(A, B) of the cable box as the figure shown.

Lock the coverplate(13), and verify the lift rod(17) on the faucet is linked correctly with the drain body through the cable.


NOTE: Do not reposition the drain if plumbers putty or other sealants applied after the locknut is tightened, or you may break the putty seal. Wipe away excess plumbers putty.

如何安装排水器
(仅对于**37329K**)

先将锁紧螺母(18)、塑料垫片(19)、橡胶垫圈(20)和尾管(22)从排水本体上依次取下。在尾管螺纹处须缠绕足以密封的密封胶带或涂合适的密封胶，装回排水本体。

把排水本体从脸盆上部孔插入。依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从排水本体底部装入。将锁紧螺母锁紧。**注意：**在锁紧螺母拧紧后，不可调整排水本体的位置，否则会破坏油灰密封或密封剂密封。

注意：如果需要，可直接在排水器盘片(23)底面沿周围涂一圈密封油灰或其它密封剂，而不使用橡胶垫片(21)。



How to Install the Drain
(Only for **37329K**)

Remove the locknut(18), plastic washer (19), rubber gasket(20) and tailpiece (22) from the drain body. Apply enough tape or sealants to tailpiece thread. Reinstall the tailpiece.

Insert the drain body into the lavatory. Put the rubber gasket (Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut. **NOTE:** Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal.


NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(23), instead of using rubber washer(21).

安装结果检查

检查并确保所有的衔接处都已拧紧。确保把手在关闭位置。

打开排水系统和主要供水源，检查并修理有漏水的接口。

用工具(24)将起泡器(25)拆下，打开龙头的冷热水，让水流出约一分钟以清除杂质。冲洗起泡器，关闭龙头，重新装回起泡器。



Ensure all connections are tightened and the handle is in the off position.

Open the drain. Turn on main water supply and check for leaks. Repair as needed.

Remove the aerator(25) with the key (24). Turn on the faucet. Run hot and cold water through the spout for about one minute to remove any debris. Remove debris from the aerator. Shut off the faucet and reinstall the aerator.

清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.