

# Mira Vie

## Electric Shower

Consistent, all-year round performance and suitable for any system, it's the ultimate in reliability.



### Product Information

Description	Colour	Product No.
Mira Vie 8.5 kW	White/Chrome	1.1788.004
Mira Vie 9.5 kW	White/Chrome	1.1788.005
Mira Vie 10.8 kW	White/Chrome	1.1788.006
Mira Vie 8.5 kW	Chrome	1.1788.512
Mira Vie 9.5 kW	Chrome	1.1788.513
Mira Vie 10.8 kW	Chrome	1.1788.514

### Features & Benefits

#### Temperature control

Pressure stabilised temperature control

#### Easy to fit

Retrofits onto inlets of most Mira electric showers

Left-hand water and cable entry points

Adjustable slide bar fits over holes left by previous shower kit

#### Easy to service

Easy filter access

#### For your customer

Separate power and temperature controls

Push button on/off

Eco setting saves water and energy

Mira Clearscale™ reduces limescale by up to 50%

Single spray showerhead with rub-clean nozzles

Modern aesthetics with chrome detailing



To download other resources, and for more information and advice on our products just visit:  
[www.mirashowers.co.uk](http://www.mirashowers.co.uk)

# Product Specification

## Tech Details

### Temperature Control

Control type: Pressure stabilised

### Installation

Power options: 8.5 kW 240V AC (7.8 kW 230V AC)

- 9.5 kW 240V AC (8.7 kW 230V AC)
- 10.8 kW 240V AC (9.9 kW 230V AC)

Supply voltage: 230v ± 10%

Supply rating: 40 amp (8.5 & 9.5 kW); 45 amp (10.8 kW)

Terminal Block connections: Maximum 16 mm<sup>2</sup>

Water entry points: Left (rising, falling & rear)

Cable entry points: Left (rising, falling & rear)

Inlet connections: 15 mm plastic stub, compression or push-fit fittings

Outlet connections: ½" BSP Male

### Supply Conditions (hot and cold)

Minimum maintained pressure: 8.5 & 9.5 kW: 0.7 bar (7 metre head); 10.8 kW: 1 bar (10 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

### Performance

Temperature stability: ± 6°C

### Safety Features

Phased shutdown: No

Factory set to safe max temp: No

Mira Sensi-flo™: No

### Accessories

Wide range of accessories available at [www.mirashowers.co.uk](http://www.mirashowers.co.uk)

### Approvals


Energy Efficiency: Class A

Kiwa certified

WRAS approved (Water Regulations Advisory Scheme)



## Dimensions



To download other resources, and for more information and advice on our products just visit: [www.mirashowers.co.uk](http://www.mirashowers.co.uk)

