

3868T 12178T 12179T 37270T 15344T 手持花洒

安装之前

BEFORE YOU BEGIN

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

Please leave these instructions for the consumer. They contain important information.

注意事项：


NOTES:

- 1.一定要先彻底冲洗供水管以清除管道中的杂质。
- 2.花洒最高工作压力：0.5Mpa(5bar)。水压超过0.5Mpa(5bar)须安装减压阀。花洒最高工作温度及环境温度：60°C。请特别注意花洒同花洒连接的笔管须远离加热器，否则可能损坏花洒及其密封件，甚至对使用者造成伤害。

1. Flush the water supply pipes thoroughly to remove debris.
2. The highest working pressure for spray is 0.5Mpa(5 bar). If it exceeds 0.5Mpa(5 bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep handspray, showerhead and the shower arm away from heater, or it may become damaged and cause injury to the user.


安装尺寸

ROUGH-IN DIMENSIONS



安装步骤

将限流器(1-1, 仅对于12179T; 1-2, 仅对于15344T)如图所示方向塞入手持花洒(2)进水口。将垫片(3, 客户自备)放入软管(4, 客户自备)接头内, 将手持花洒旋紧到软管上, 软管另一端连接水源。



注意: 如水压太低, 则不必安装限流器。

INSTALLATION


Put the restrictor(1-1, for 12179T only; 1-2, for 15344T only) into the handspray(2) inlet. Put the washer(3, not provided) into the shower hose(4, not provided) connector, screw the handspray(2) to the shower hose. Connect another end of shower hose to the water supply.

NOTE: If working pressure is too low, restrictor is not needed.

使用说明

如何清洗喷孔水垢, 杂质

喷孔杂质或结垢会导致水流变形, 流量变小。打开水源, 用力按压或摩擦橡胶喷孔, 去除杂质或水垢。



OPERATING INSTRUCTIONS

How to Clean the Nozzles

Any debris or mineral build-up may cause the flow stream to become distorted or reduce the flowrate. To remove the debris or mineral build-up, run water through the handspray, firmly press or rub your finger back and forth across the rubber nozzles.

清洗说明

适用于所有加工处理过的表面: 以中性肥皂水清洗镀层表面, 再以干净的软布彻底擦干整个表面, 许多清洁剂, 比如氨水、去污粉及洁厕灵等, 会对电镀表面造成伤害, 切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc, which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

零件图

SERVICE PARTS



**订购时请说明颜色编号

**Color code must be specified when ordering